

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2010

© COPYRIGHT 2010

Tyco Electronics AMP GmbH

ALL RIGHTS RESERVED.

NOTES:

1 MATERIAL: POLYAMIDE GLASS FILLED
COLOUR NATURAL

2 MATERIAL: POLYAMIDE GLASS FILLED
COLOUR BLACK

3) NET WEIGHT: ~4.8 g

4) VOLUME: ~3450 mm^3

5) PACKAGING: SEE TE PACKAGING SPECIFICATION
107-20294

6 TE LOGO

7 TE PART NUMBER

8 CONDUCTOR SIZE AND CURRENT RATING

9 N CODE

10 L CODE

11 PE CODE

12 RATED VOLTAGE



13 DATE CODE

14 AREA FOR AGENCY APPROVAL LOGO




15 CAVITY MOULD ID

16 PART NOT YET TOOLED AND RELEASED
FOR PRODUCTION

17) FOR CABLE TYPE AND CABLE RANGE REFER TO
CUSTOMER DRAWING 293607



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G1	REVISED MARKINGS	05NOV2012	MZ	JC
	G2	PARTS -2, -3, 1-2, 1-3 RELEASED FOR PRODUCTION	26JUN2013	KR	JC
	G3	REVISED PART NUMBERS	21JUL2017	SK	ZM
	G4	REVISED PER ECR-18-006945	20SEP2018	SR	MZ



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. ZUCCA 06OCT2009	 TE Connectivity		
DIMENSIONS: mm		CHK M. ZUCCA 06OCT2009			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G. TURCO 06OCT2009			
0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.20 3 PLC ±0.20 4 PLC ±0.20 ANGLES ±3° FINISH -		PRODUCT SPEC 108-20304 APPLICATION SPEC 114-20152 WEIGHT NOTE 3			
MATERIAL SEE NOTES		NAME PIN HOUSING FREE HANGING NECTOR* M-LINE 3 POSITIONS UNSEALED VERSION		SIZE A300779	CAGE CODE C-293469
Customer Drawing		SCALE 2:1		SHEET 1	OF 2
		REV G4			

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
1	-		-	SEE SHEET 1	-	-

POLARIZATION TYPES







TYPE "A"	TYPE "B"
	
P / Ns : 0-293469-1, 1-293469-1	P / Ns : 0-293469-2, 1-293469-2
TYPE "C"	TYPE "D"
	
P / Ns : 0-293469-3, 1-293469-3	P / Ns : 0-293469-4 , 1-293469-4

TABLE 1						
OBSOLETE		D	BLACK	PIN HOUSING FREE HANGING VERSION NECTOR* M-LINE	F	1-293469-4
		C	BLACK	PIN HOUSING FREE HANGING VERSION NECTOR* M-LINE	G	1-293469-3
		B	BLACK	PIN HOUSING FREE HANGING VERSION NECTOR* M-LINE	G	1-293469-2
		A	BLACK	PIN HOUSING FREE HANGING VERSION NECTOR* M-LINE	G	1-293469-1
OBSOLETE		D	NATURAL	PIN HOUSING FREE HANGING VERSION NECTOR* M-LINE	F	0-293469-4
		C	NATURAL	PIN HOUSING FREE HANGING VERSION NECTOR* M-LINE	G	0-293469-3
		B	NATURAL	PIN HOUSING FREE HANGING VERSION NECTOR* M-LINE	G	0-293469-2
		A	NATURAL	PIN HOUSING FREE HANGING VERSION NECTOR* M-LINE	G	0-293469-1
NOTE		POL. KEYING	COLOUR	DESCRIPTION	REV.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±°
1 PLC ±0.3
2 PLC ±0.20
3 PLC ±°
4 PLC ±°
ANGLES ±3°
FINISH -

MATERIAL

SEE NOTES

DWN
M. ZUCCA
CHK
M. ZUCCA
APVD
G. TURCO

06OCT2009
06OCT2009
06OCT2009

PRODUCT SPEC
108-20304
APPLICATION SPEC
114-20152
WEIGHT
NOTE 3

Customer Drawing

TE Connectivity

NAME
PIN HOUSING FREE HANGING
NECTOR* M-LINE
3 POSITIONS UNSEALED VERSION

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-293469

RESTRICTED TO
-

SCALE
2:1

SHEET
2

OF
2

REV
G4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[293469-1](#)