



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
1	-		-	SEE SHEET 1	-	-

PLARIZATION KEYS

TYPE "A"




TYPE "B"




P/Ns: 0-293598-1,
1-293598-1, 2-293598-1

P/Ns: 0-293598-2,
1-293598-2, 2-293598-2

TYPE "C"



TYPE "D"



P/Ns: 0-293598-3,
1-293598-3, 2-293598-3

P/Ns: 0-293598-4,
1-293598-4, 2-293598-4

OBSOLETE	67	D	BLACK	2	PIN HSG PANEL MOUNT VERS. NECTOR* M-LINE	A	2-293598-4
	67	C	BLACK	2	PIN HSG PANEL MOUNT VERS. NECTOR* M-LINE	D	2-293598-3
	67	B	BLACK	2	PIN HSG PANEL MOUNT VERS. NECTOR* M-LINE	D	2-293598-2
	67	A	BLACK	2	PIN HSG PANEL MOUNT VERS. NECTOR* M-LINE	D	2-293598-1
	40	D	BLACK	2	PIN HSG PANEL MOUNT VERS. NECTOR* M-LINE	G	1-293598-4
	40	C	BLACK	2	PIN HSG PANEL MOUNT VERS. NECTOR* M-LINE	G	1-293598-3
OBSOLETE	40	B	BLACK	2	PIN HSG PANEL MOUNT VERS. NECTOR* M-LINE	G	1-293598-2
	40	A	BLACK	2	PIN HSG PANEL MOUNT VERS. NECTOR* M-LINE	G	1-293598-1
	40	D	NATURAL	1	PIN HSG PANEL MOUNT VERS. NECTOR* M-LINE	G	0-293598-4
	40	C	NATURAL	1	PIN HSG PANEL MOUNT VERS. NECTOR* M-LINE	G	0-293598-3
	40	B	NATURAL	1	PIN HSG PANEL MOUNT VERS. NECTOR* M-LINE	G	0-293598-2
	40	A	NATURAL	1	PIN HSG PANEL MOUNT VERS. NECTOR* M-LINE	G	0-293598-1
IP DEGREE CODE		POL. KEYING	COLOUR	MATERIAL	DESCRIPTION	REV.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.3
1 PLC ±0.3
2 PLC ±0.20
3 PLC ±0.20
4 PLC ±0.20
ANGLES ±3°
FINISH -

MATERIAL

SEE NOTES

DWN
M. ZUCCA
CHK
M. ZUCCA
APVD
G. TURCO

29OCT2009
29OCT2009
29OCT2009

PRODUCT SPEC
108-20304
APPLICATION SPEC
114-20452
WEIGHT
~6.2 g

Customer Drawing

TE Connectivity

PIN HOUSING
PANEL MOUNT VERSION
NECTOR* M-LINE

SIZE
A300779

CAGE CODE
C-293598

DRAWING NO

RESTRICTED TO



SCALE
2:1

SHEET
2


OF
4


REV
G1

LOC 	DIST -	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-



PANEL / WALL
SUGGESTED CUT OUT




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. ZUCCA	29OCT2009	 TE Connectivity							
DIMENSIONS: mm		CHK M. ZUCCA	29OCT2009	NAME PIN HOUSING PANEL MOUNT VERSION NECTOR* M-LINE							
		APVD G. TURCO	29OCT2009								
		PRODUCT SPEC 108-20304		SIZE A300779		CAGE CODE C=293598		DRAWING NO RESTRICTED TO -			
APPLICATION SPEC 114-20452											
MATERIAL SEE NOTES		WEIGHT ~6.2 g									
TOLERANCES UNLESS OTHERWISE SPECIFIED:		Customer Drawing		SCALE 2:1		SHEET 3		OF 4		REV G1	
0 PLC ±-											
1 PLC ±0.3											
2 PLC ±0.20											
3 PLC ±-											
4 PLC ±-											
ANGLES ±3°											
FINISH -											

LOC 	DIST -	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-


PANEL / WALL
SUGGESTED CUT OUT FOR
MULTIPLE HOLES ON MULTIPLE ROWS

(PITCH CAN BE ADJUSTED TO CUSTOMER
NEED BUT IN ANY CASE MUST NOT BE LESS
THAN 30.00 mm)



PANEL / WALL
SUGGESTED CUT OUT FOR
MULTIPLE HOLES ON SINGLE ROW

(PITCH CAN BE ADJUSTED TO CUSTOMER
NEED BUT IN ANY CASE MUST NOT BE LESS
THAN 30.00 mm)



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±°

1 PLC ±0.3

2 PLC ±0.20

3 PLC ±°

4 PLC ±°

ANGLES ±3°

FINISH -

DWN
M. ZUCCA
CHK
M. ZUCCA
APVD
G. TURCO

29OCT2009
29OCT2009
29OCT2009

PRODUCT SPEC
108-20304

APPLICATION SPEC
114-20452

WEIGHT
~6.2 g

Customer Drawing

TE Connectivity

NAME

PIN HOUSING
PANEL MOUNT VERSION
NECTOR* M-LINE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C=293598

-

SCALE

2:1

SHEET

4

OF

4

REV

G1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-293598-1](#)