

REVISIONS						
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	M	REVISED PER ECO-16-001979	15FEB2016	NK	MZ	
	N	REVISED PER ECO-17-013721	16NOV2017	RS	MZ	



- | | |
|----|---|
| 14 | PRODUCT IS SOLD BY THE FOOT. |
| 15 | FINISH: PREPLATED SILVER 200 uIN MIN, OVER NICKEL .040 uIN MIN. |
| 16 | REELED PRODUCT. |
| 17 | PRELIMINARY PART NUMBER. |
| 18 | OBSOLETE PART NUMBER. |
| 19 | OBSOLETEPARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINIS |

18	NOT AVAILABLE			--	--	--	--	--	03088	4-192039-5	
	NOT AVAILABLE			--	--	--	--	--	03087	4-192039-4	
	NOT AVAILABLE			--	--	--	--	--	03051	4-192039-3	
	NOT AVAILABLE			--	--	--	--	--	03050	4-192039-2	
19 OBSOLETE	B	[.036]	[.58]	12	16.51[.650]	UNPL	43	0.20[.008]	03119	4-192039-1	
	B	[.032]	[.58]	12	14.22[.560]	1-2	43	0.15[.006]	03124	4-192039-0	
18	NOT AVAILABLE			--	--	--	--	--	--	3-192039-9	
19 OBSOLETE	B	[.038]	[.46]	12	12.7[.500]	--	34	0.20[.008]	03122	3-192039-8	
	B	[.038]	[.46]	12	12.7[.500]	1-2	34	0.20[.008]	03121	3-192039-7	
	B	[.038]	[.46]	12	12.7[.500]	UNPL	34	0.20[.008]	03048	3-192039-6	
	B	[.032]	[.46]	12	12.7[.500]	1-2	--	0.15[.006]	03129	3-192039-5	
OBSOLETE	B	[.032]	[.46]	12	12.7[.500]	UNPL	34	0.15[.006]	03110	3-192039-4	
19 OBSOLETE	B	[.034]	[.33]	12	9.52[.375]	1-2	24	0.20[.008]	03148	3-192039-3	
18	--					--	--	--	03042	3-192039-2	
	SUPERSEDED BY 2-192039-7					--	--	--	--	03041	3-192039-1
	B	[.036]	[.31]	12	7.9[.311]	3-2	21	0.20[.008]	03082	3-192039-0	
19 OBSOLETE	B	[.036]	[.31]	12	7.9[.311]	1-2	21	0.20[.008]	03036	2-192039-9	
				--	--	--	--	--	03035	2-192039-8	
19 OBSOLETE	B	[.036]	[.31]	12	7.9[.311]	UNPL	21	0.20[.008]	03066	2-192039-7	
19 OBSOLETE	B	[.036]	[.30]	12	7.37[.291]	UNPL	20	0.20[.008]	03120	2-192039-6	
18	NOT AVAILABLE			--	--	--	--	--	03034	2-192039-5	
18	NOT AVAILABLE			--	--	--	--	--	03030	2-192039-4	
OBSOLETE	B	[.036]	[.30]	12	6.3[.248]	1-2	17	0.20[.008]	03027	2-192039-3	
	B	[.036]	[.30]	12	6.3[.248]	UNPL	17	0.20[.008]	03026	2-192039-2	
19 OBSOLETE	B	[.033]	[.27]	12	6.3[.248]	1-2	16	0.20[.008]	03140	2-192039-1	
	B	[.033]	[.27]	12	6.3[.248]	UNPL	16	0.20[.008]	03139	2-192039-0	
	B	[.036]	[.25]	12	6.0[.236]	3-2	15	0.20[.008]	03024	1-192039-9	
	B	[.034]	[.20]	12	4.0[.157]	4	9	0.20[.008]	03017	1-192039-8	
OBSOLETE	B	[.034]	[.20]	12	4.0[.157]	3-2	9	0.20[.008]	03016	1-192039-7	
19 OBSOLETE	B	[.034]	[.20]	12	4.0[.157]	UNPL	9	0.20[.008]	03071	1-192039-6	
	--					--	--	--	03015	1-192039-5	
	B	[.032]	[.20]	12	4.0[.157]	3-2	9	0.15[.006]	03014	1-192039-4	
	B	[.032]	[.20]	12	4.0[.157]	4	9	0.15[.006]	03128	1-192039-3	
	B	[.032]	[.20]	12	4.0[.157]	UNPL	9	0.15[.006]	03073	1-192039-2	
	B	[.020]	[.20]	13	4.0[.157]	UNPL	9	0.12[.005]	03091	1-192039-1	
	C	[.038]		12	--	3-2	--	0.20[.008]	03115	1-192039-0	
18	NOT AVAILABLE			12	--	--	--	--	--	192039-9	
19 OBSOLETE	C	[.038]		12	--	1-2	--	0.20[.008]	03116	192039-8	
OBSOLETE	C	[.038]		12	--	UNPL	--	0.20[.008]	03078	192039-7	
18 OBSOLETE	C	[.034]		12	--	3-2	--	0.15[.006]	03003	192039-6	
	C	[.034]		12	--	1-2	--	0.15[.006]	03094	192039-5	
	C	[.034]		12	--	UNPL	--	0.15[.006]	03057	192039-4	
	C	[.020]		13	--	UNPL	--	0.12[.005]	03138	192039-3	
OBSOLETE				--	--	--	--	--	03079	192039-2	
18	NOT AVAILABLE			--	--	--	--	--	03067	192039-1	
	STYLE	LH	FREE DIA	MAT'L (NOTE)	MATING DIA REF	PLATING	NUM LOUV	MAT'L THK	REF	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RA JAYNE 09-12-91		 TE Connectivity			
		CHK RA JAYNE 09-12-91					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CONTACT BAND, LAIIS, MALE			
		APVD —				NAME	
		PRODUCT SPEC —					
		APPLICATION SPEC —					
MATERIAL SEE TABLE		FINISH —		SIZE A2	CAGE CODE 00779	DRAWING NO C=192039	RESTRICTED TO —
		WEIGHT —		SCALE NTS		SHEET 1 of 2	REV N
		CUSTOMER DRAWING					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-192039-1](#)