






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	R	REVISED PER ECO-21-006945	28OCT2021	RK	MZ



RECOMMENDED PANEL CUTOUT

DETAIL A



DETAIL B

#4-40 THREADED INSERTS		NO	A	206705-7
Ø3.18 (.125) HOLES	3	NO	A	206705-5
Ø3.18 (.125) HOLES	-	YES	B	206705-4
	-	YES	A	206705-3
	-	NO	B	206705-2
	-	NO	A	206705-1
MOUNTING FEATURE	NOTES	PERIPHERAL SEAL	SEE DETAIL	PART NUMBER

- 1 CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
2 RECEPTACLE WILL ACCEPT NINE (9) MULTIMATE PIN CONTACTS.
3 WHITE DOT OVER MAJOR KEY, APPROX WHERE SHOWN.
4 OBSOLETE PART NUMBER.
5 MATERIALS
HOUSING: PA66, BLACK
PERIPHERAL SEAL: NITRILE BUTADIENE RUBBER, BLACK
THREADED INSERTS: BRASS

6 TE LOGO AND PART NUMBER LOCATED ON ANY FLANGE EDGE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.HARDY 05/19/94	TE Connectivity	
DIMENSIONS: MM [INCHES]		CHK R.STONE 05/20/94		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME	
0 PLC ± -		PRODUCT SPEC		
1 PLC ± -		108-10024	RECEPTACLE HOUSING, STANDARD SEX, SHELL SIZE 13, CPC	
2 PLC ± 0.13 [.005]		APPLICATION SPEC		
3 PLC ± -		-	SIZE A2	CAGE CODE 00779
4 PLC ± -		WEIGHT -	DRAWING NO C-206705	RESTRICTED TO -
ANGLES ± -		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1
FINISH -			REV R	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[206705-3](#)