





2		1					
LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	REVISED PER E.O. PI7000	08DEC2000	SP	RDR
			D	REVISED PER E.O. PI9555	11JUL2007	JA	RDR
			E	REVISED PER E.O. P20396	26JUN2010	JA	RDR
			F	REVISED PER ECO-15-007761	28MAY2015	RL	DM



DEUTSCH
IDENTIFICATION
MARKING




SECTION A-A
WIRE BARREL



SECTION B-B
INSULATION BARREL

- 3 MATERIAL:
BODY: .012 [0.30] THICK COPPER ALLOY
SLEEVE: STAINLESS STEEL
2. WIRE RANGE: 18 AWG TO 14 AWG [0.75-2.0 mm²]
INSULATION RANGE: $\varnothing .095$ -.150 [$\varnothing$ 2.41-3.81]
- 1 APPLIES ONLY TO SELECTIVE GOLD 1062-14-0144.
INDICATED DIMENSION SHOWS GOLD PLATED AREA.
- NOTES: UNLESS OTHERWISE SPECIFIED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	M. BLUM	04NOV1999
DIMENSIONS: INCHES[mm]		CHK	VLADIMIR TOMSA	04DEC2000
		APVD	R. REED	08DEC2000
		PRODUCT SPEC		
		0425-015-0000		
MATERIAL		APPLICATION SPEC		
		114-151000		
		WEIGHT		
		0.44 g		
FINISH		Customer Drawing		
SEE TABLE				

TE INTERNAL PN		DEUTSCH PN	PLATING	
1062-14-0122		1062-14-0122	NICKEL	
1062-14-0144		1062-14-0144	SELECTIVE GOLD	
1062-14-0177		1062-14-0177	TIN	
TE Connectivity				
NAME SOCKET, STAMPED AND FORMED SIZE 16 14-18AWG				
SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO
A3	4AFU8	C-1062-14-01XX		-
		SCALE	SHEET	REV
		6:1	1 OF 1	F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1062-14-0144 \(Mouser Reel\)](#) [1062-14-0144 \(Cut Strip\)](#) [1062-14-0144 \(Loose Piece\)](#)