










LOC	REV	REVISIONS			
		P	LYN	DESCRIPTION	DATE
A1	-	M	PCN-E-12-017366		090CT2012
		M1	PCN-E-14-012222		13AUG2016
		M2	PCN-E-16-006166		27APR2016




CONNECTOR WITH
OPENED SHIELD

VOID CORING OPTIONAL
Materialentnahme optional



- ⚠ Siehe Tabelle auf Seite 2
SEE TABLE ON SHEET 2
- ⚠ SEE PAGE 2
Siehe Blatt 2
- ⚠ SPACER IN PRESET POSITION
Spacer in Vorabstellung
- ⚠ WARPAGE ALLOWED DOWN TO 35.7MM
Einfall bis 35.7 mm zulässig
- ⚠ Signal Kontakte sind ausgelegt fuer Kabelgrossen AWG 18-20, Leiterquerschnitt 0.5 - 0.75mm.
Für die Gültigkeit der Steckverbinder ist notwendig, dass der Isolationsdurchmesser 1.4 - 1.5mm beträgt.
SIGNAL CONTACTS ARE SUITABLE FOR WIRE SIZE AWG 18-20, CONDUCTOR CROSS SECTION 0.5 - 0.75mm.
FOR THE SEALING OF THE CONNECTOR IS NECESSARY A CABLE ISOLATION DIAMETER OF 1.4 - 1.5mm.



2R8T-14A464-KD-XXX	X-1355628-X	1x FAMILY SEALING	8
		1x PERIPHERAL SEAL	7
		1x WIRE DRESS COVER	6
		1x COVER FAM.-SEAL	5
		1x RIGHT SLIDE	4
		1x LEFT SLIDE	3
		1x SPACER	2
FORD PN	TE- PN	1x HOUSING	1
		DESCRIPTION	

THIS DRAWING IS A CONTROLLED DOCUMENT.				B. LOCHNER 04JUL00 CH. JÄRKLIN 04JUL00 G. MUMMER 04JUL00			
DIMENSIONS: UNIT: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		TE Connectivity	
0 PLC	±0.4	1 PLC	±0.4	PRODUCT SPEC		SOCKET HOUSING 47WAY MK25/60 ABS CONNECTOR WITH MATING AREA	
2 PLC	±0.4	2 PLC	±0.4	APPLICATION SPEC		SIZE	CASE CODE
4 PLC	±0.4	4 PLC	±0.4	ANGLES		A0 00779	C=1355628
MATERIAL		FINISH		WEIGHT		RESTRICTED TO	
				Customer Drawing		SCALE	5:1
						SHEET	1 of 2
						REV	M2

8		7		6		5		4		3		2		1	
THIS DRAWING IS UNPUBLISHED										RELEASED FOR PUBLICATION					
© 1991 GM copyright date										ALL RIGHTS RESERVED					
LOC		DISP		REVISONS											
A1		-		P		LTN		DESCRIPTION		DATE		DWN		APPR	
				-		SEE SHEET 1				-		-		-	

</

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1355628-4](#)