





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B5	REVISED PER ECR-16-011494	20JUN2017	NK	CX




- ① MATERIAL: CONTACTS - BRASS
HOUSING - UL 94V-O RATED HIGH TEMP NYLON, COLOR BLACK.
- ② PLATING: CONTACTS - 2.54 μ m MINIMUM TIN-LEAD OVER 1.27 μ m MINIMUM NICKEL.
- ④ RECOMMENDED PC BOARD THICKNESS OF 1.57.
- ⑤ RETENTION BUMP FEATURES FACE EACH OTHER, TYPICAL ALL CONFIGURATIONS.
- ⑥ PLATING: CONTACTS - 2.54 μ m MINIMUM MATTE TIN OVER 1.27 μ m MINIMUM NICKEL.
- ⑦ SELECTIVE LOADED CONFIGURATION.



											
1				4				7			10
1, 4, 7, 10					4-1445050-0						
PIN INSERTED					PART NUMBER						

△7	△6	1, 4, 7, 10	27.00	33.14	31.00	10	4-1445050-0
	△6	1, 2, 11, 12	33.00	39.14	37.00	12	3-1445050-2
	△6	1, 2, 9, 10	30.00	36.14	34.00	11	3-1445050-1
	△6	1, 2, 9, 10	27.00	33.14	31.00	10	3-1445050-0
	△6	1, 2, 7, 8	24.00	30.14	28.00	9	2-1445050-9
	△6	1, 2, 7, 8	21.00	27.14	25.00	8	2-1445050-8
	△6	1, 2, 5, 6	18.00	24.14	22.00	7	2-1445050-7
	△6	1, 2, 5, 6	15.00	21.14	19.00	6	2-1445050-6
	△6	1, 2, 3, 4	12.00	18.14	16.00	5	2-1445050-5
	△6	1, 2, 3, 4	9.00	15.14	13.00	4	2-1445050-4
	△6	1, 2	6.00	12.14	10.00	3	2-1445050-3
	△6	1, 2	3.00	9.14	7.00	2	2-1445050-2
0-2	△2	1, 2, 11, 12	33.00	39.14	37.00	12	+1445050-2-
0-1	△2	1, 2, 9, 10	30.00	36.14	34.00	11	+1445050-1-
0-0	△2	1, 2, 9, 10	27.00	33.14	31.00	10	+1445050-0-
0-9	△2	1, 2, 7, 8	24.00	30.14	28.00	9	+1445050-9-
0-8	△2	1, 2, 7, 8	21.00	27.14	25.00	8	+1445050-8-
0-7	△2	1, 2, 5, 6	18.00	24.14	22.00	7	+1445050-7-
0-6	△2	1, 2, 5, 6	15.00	21.14	19.00	6	+1445050-6-
0-5	△2	1, 2, 3, 4	12.00	18.14	16.00	5	+1445050-5-
0-4	△2	1, 2, 3, 4	9.00	15.14	13.00	4	+1445050-4-
0-3	△2	1, 2	6.00	12.14	10.00	3	+1445050-3-
0-2	△2	1, 2	3.00	9.14	7.00	2	+1445050-2-
	FINISH	CON POS W/RET BUMP△5	DIM Z	DIM V	DIM L	NO. OF POSN	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ROOT 08OCT2000	 TE Connectivity	
		CHK K. WHITAKER 19OCT2000		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1445050-1](#)