



REVISIONS					
P	LTR	DESCRIPTION	DATE	OWN	APVD
	B2	REVISED PER ECR-16-011494	20JUN2017	NK	CX



- ① MATERIAL: CONTACTS - BRASS
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
HOLDDOWNS: - PHOSPHOR BRONZE.
- ② PLATING: CONTACTS - 0.38 μ m MINIMUM GOLD ON MATING END,
2.54 μ m MINIMUM TIN LEAD ON SOLDER TAILS, BOTH OVER
1.27 μ m MINIMUM NICKEL.
HOLDDOWNS: 2.54 μ m MINIMUM TIN-LEAD OVER 1.27 μ m MINIMUM
NICKEL.
- ④ RECOMMENDED PC BOARD THICKNESS OF 1.57.
- ⑤ PLATING: CONTACTS - 0.38 μ m MINIMUM GOLD ON MATING END,
2.54 μ m MINIMUM MATTE TIN ON SOLDER TAILS, BOTH OVER
1.27 μ m MINIMUM NICKEL.
HOLDDOWNS: 2.54 μ m MINIMUM MATTE TIN OVER 1.27 μ m MINIMUM
NICKEL.



	33.00	40.41	40.00	12	3-1445091-2
	30.00	37.41	37.00	11	3-1445091-1
	27.00	34.41	34.00	10	3-1445091-0
	24.00	31.41	31.00	9	2-1445091-9
	21.00	28.41	28.00	8	2-1445091-8
	18.00	25.41	25.00	7	2-1445091-7
	15.00	22.41	22.00	6	2-1445091-6
	12.00	19.41	19.00	5	2-1445091-5
	9.00	16.41	16.00	4	2-1445091-4
	6.00	13.41	13.00	3	2-1445091-3
	3.00	10.41	10.00	2	2-1445091-2

SUPERSEDED BY 3-1445091-2		33.00	40.41	40.00	12	1-1445091-2-
SUPERSEDED BY 3-1445091-1		30.00	37.41	37.00	11	1-1445091-1-
SUPERSEDED BY 3-1445091-0		27.00	34.41	34.00	10	1-1445091-0-
SUPERSEDED BY 2-1445091-9		24.00	31.41	31.00	9	1-1445091-9-
SUPERSEDED BY 2-1445091-8		21.00	28.41	28.00	8	1-1445091-8-
SUPERSEDED BY 2-1445091-7		18.00	25.41	25.00	7	1-1445091-7-
SUPERSEDED BY 2-1445091-6		15.00	22.41	22.00	6	1-1445091-6-
SUPERSEDED BY 2-1445091-5		12.00	19.41	19.00	5	1-1445091-5-
SUPERSEDED BY 2-1445091-4		9.00	16.41	16.00	4	1-1445091-4-
SUPERSEDED BY 2-1445091-3		6.00	13.41	13.00	3	1-1445091-3-
SUPERSEDED BY 2-1445091-2		3.00	10.41	10.00	2	1-1445091-2-

	FINISH	DIM Z	DIM V	DIM W	NO. OF POSN	PART NUMBER
--	--------	-------	-------	-------	----------------	-------------



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09OCT2000 J.ROOT		TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.13 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		NAME RIGHT ANGLE SURF MOUNT HEADER ASSY, 0.38 MIC GOLD CONTACTS, W/SURF MNT, HOLDDONWS, SGL ROW, MICRO MATE-N-LOK™	
		PRODUCT SPEC -		SIZE CAGE CODE DRAWING NO A200779 C-1445091	
MATERIAL 		FINISH SEE TABLE		RESTRICTED TO -	
		WEIGHT -		SCALE 5:1 SHEET 1 OF REV B2	
		CUSTOMER DRAWING			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1445091-2](#)