





THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A3	REVISED PER ECR-16-011494	30MAY2017	NK	CX




- 1 MATERIAL: CONTACTS - BRASS
HOUSING - UL 94V-O RATED HIGH TEMP NYLON, COLOR BLACK.
- 2 PLATING: CONTACTS - 0.76 μ m MINIMUM GOLD ON MATING END,
2.54 μ m MINIMUM TIN LEAD ON SOLDER TAILS, BOTH OVER
1.27 μ m MINIMUM NICKEL.
- 3 DATUMS AND BASIC DIMENSIONS ARE ESTABLISHED BY CUSTOMER.
- 4 RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 5 PLATING: CONTACTS - 0.76 μ m MINIMUM GOLD ON MATING END,
2.54 μ m MINIMUM MATTE TIN ON SOLDER TAILS, BOTH OVER
1.27 μ m MINIMUM NICKEL.


		33.00	28.70	33.00	40.14	12	3-1445098-2
		30.00	25.70	30.00	37.14	11	3-1445098-1
		27.00	22.70	27.00	34.14	10	3-1445098-0
		24.00	19.70	24.00	31.14	9	2-1445098-9
		21.00	16.70	21.00	28.14	8	2-1445098-8
		18.00	13.70	18.00	25.14	7	2-1445098-7
		15.00	10.70	15.00	22.14	6	2-1445098-6
		12.00	7.70	12.00	19.14	5	2-1445098-5
		9.00	4.70	9.00	16.14	4	2-1445098-4
		-	-	6.00	13.14	3	2-1445098-3
		-	-	3.00	10.14	2	2-1445098-2
9		33.00	28.70	33.00	40.14	12	1-1445098-2
		30.00	25.70	30.00	37.14	11	1-1445098-1
0		27.00	22.70	27.00	34.14	10	1-1445098-0
9		24.00	19.70	24.00	31.14	9	1445098-9
8		21.00	16.70	21.00	28.14	8	1445098-8
7		18.00	13.70	18.00	25.14	7	1445098-7
6		15.00	10.70	15.00	22.14	6	1445098-6
5		12.00	7.70	12.00	19.14	5	1445098-5
4		9.00	4.70	9.00	16.14	4	1445098-4
3		-	-	6.00	13.14	3	1445098-3
2		-	-	3.00	10.14	2	1445098-2
	FINISH	DIM Z	DIM V	DIM T	DIM W	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN J. ROOT	09OCT2000		 TE Connectivity				
DIMENSIONS: mm			CHN K. WHITAKER	17-APR-2001		NAME RIGHT ANGLE THRU HOLE HEADER ASSY, 0.76 MIC GOLD CONTACTS, W/PLASTIC™ HOLDDOWNS, SGL ROW, MICRO MATE-N-LOK				
			APVD C. JONES	17-APR-2001						
			PRODUCT SPEC		SIZE A2					
			APPLICATION SPEC							
TOLERANCES UNLESS OTHERWISE SPECIFIED:			-		CAGE CODE		DRAWING NO			
0 PLC ±. 1 PLC ±. 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±.			-		00779		G-1445098			
MATERIAL			WEIGHT		RESTRICTED TO		-			
			-		-		-			
FINISH			CUSTOMER DRAWING		SCALE		SHEET			
SEE TABLE					5:1		1 OF 2			
					REV		A3			


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



PCB LAYOUT FOR 2 POSITION 
COMPONENT SIDE



PCB LAYOUT FOR 3 POSITION 
COMPONENT SIDE



PCB LAYOUT FOR 4-12 POSITION 
COMPONENT SIDE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1445098-8](#)