



LOC	DIST	REVISIONS 変更				DATE	DWN	APVD
J	—	P	LTR	DESCRIPTION				
			K2	REVISED PER ECR-16-000249		18JAN16	SC	DZ





注記

1. 使用ハウジングはキャップ及びプラグ
- △ 2本圧着の被覆外径は3.4mm最大
3. 取扱説明書：IS-105J
- △ 全面ニッケルメッキの上に0.76μm最小の金メッキを施す。

NOTES


1. APPLICABLE HOUSING : CAP AND PLUG.
- △ APPLICABLE INSULATION DIA METER FOR TWO-WIRE CRIMP IS 3.4mm MAX.
3. INSTRUCTION SHEET : IS-105J
- △ SELECTIVE GOLD PLATED AREA 0.76μm MIN THK OVER Ni PLATED.



170361,170362 170365,170366	170364-4	PRE TIN PHOS BRO 0.2t 錫めっき済磷青銅 0.2t	170360-4
	170364-3	BRASS 0.2t 黄銅 0.2t	170360-3
	170364-1	PRE TIN BRASS 0.2t 錫めっき済黄銅 0.2t	170360-1
かん合相手型番 MATING CON'T	ばら状態型番 LP.NO	材料 MATERIAL	型番 P/N

WIRE RANGE
絶合電線断面積AWG#22~#18
0.30~0.80mm²INSULATION DIA
被覆外径

△ 1.5~2.4mm

DIMENSIONS: 単位： 耗 mm	DWN J.SATO	18JAN2008	MATERIAL 材料		SEE TABLE	FINISH 仕上			
	CHK S.MANABE	18JAN2008	TE Connectivity						
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差	APVD S.MANABE	18JAN2008							
	PRODUCT SPEC 製品規格	108-5138	NAME 名称			MINI UNIVERSAL MATE-N-LOK PIN CONTACT			
	APPLICATION SPEC 取付適用規格	114-5050							
	0 PLC ± ±0.3	WEIGHT		SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO		
1 PLC ±			A4	00779	C-170360		—		
2 PLC ±	CUSTOMER DRAWING								
3 PLC ±									
4 PLC ±			SCALE 尺度		4:1	SHEET	1 of 1	REV	K2
ANGLES ±									
									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[170360-1](#)