

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED PER ECO-16-004435	15APR2016	KG	EO

D


D

C



C

B

B



MATING FACE






REAR FACE

1 FRONT & REAR INSULATOR: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948.
CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194
REAR GROMMET: FLUOROSILICONE ELASTOMER PER MIL-R-25988 B EXCEPT 4.6.6.1

2 DATE CODE: YEAR & WEEK (YY WW)

3. DESCRIPTIVE PART NUMBER GPRBE14SA
THIS INSERT CONTAINS: 14 CAVITIES FOR SIZE 16 SOCKET CONTACTS.
4. THIS PRODUCT IS SOLD BY TE CONNECTIVITY UNDER A LICENSE FROM RADIAL SA.

617999251	1738119-1
RADIALL PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BH	29JUN2006	 TE Connectivity			
		CHK JPM	29JUN2006				
DIMENSIONS: mm		APVD JPM	29JUN2006	NAME INSERT ASSEMBLY, SOCKET, ENVIRONMENTAL, ARRANGEMENT 14, KEY A, GPRB			
		PRODUCT SPEC -					
		APPLICATION SPEC -					
MATERIAL 		WEIGHT -		SIZE A2	CAGE CODE 00779	DRAWING NO C-1738119	RESTRICTED TO -
		CUSTOMER DRAWING		SCALE 4:1	SHEET 1	OF 1	REV A

A

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1738119-1](#)