

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		B	REVISED PER ECO-12-018187	2NOV2012	CT	KH

D

D

C


C

B

B

A

A



- 1 FRONT & REAR INSULATORS: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948. CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194, REAR GROMMET & INTERFACIAL SEAL: FLUOROSILICONE ELASTOMER PER MIL-R-25988 B EXCEPT 4.6.6.1.
- 2 PART TO MARKED WITH TE IDENTIFICATION, TE PART NO. AND DATE CODE: YEAR & WEEK (YY WW) IN APPROXIMATE AREA SHOWN.
3. THIS INSERT CONTAINS: 40 CAVITIES FOR SIZE 22 PIN CONTACTS
4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIAL SA.

NON-ENV	GPRBN40PA	1738186-3
GROMMET ONLY	GPRBH40PA	1738186-2
ENVIRONMENTAL	GPRBE40PA	1738186-1
REMARKS	DESCRIPTIVE PART NO.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS CHK K. HOGAN APVD K. HOGAN	10-4-10 10-4-10 10-4-10	TE Connectivity		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME INSERT ASSEMBLY, PIN, ARRANGEMENT 40, KEY A, GPRB		
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		SIZE A2		
MATERIAL 1				CAGE CODE 00779		
				DRAWING NO C-1738186		
				RESTRICTED TO -		
				SCALE 4:1		
				SHEET 1		
				OF 1		
				REV B		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1738186-3](#)