






NOTES

- ⓑ

ⓓ
- △







— "OPTIONAL" DEPENDING ON THE MOLD CAVITY NUMBER, THIS SHAPE COULD BE IN ONE OF THE 2 POSITIONS.

— "OPTIONNEL" CETTE FORME PEUT SE TROUVER DANS UNE DES 2 POSITIONS SELON LE No D'EMPREINTE



185001-6 KEYING E1	1	SEALED TAB HOUSING 4 POS. J.P.T.	PBT 20% GF	GREEN
185001-5 KEYING N	1	SEALED TAB HOUSING 4 POS. J.P.T.	PBT 20% GF	WHITE
185001-4 KEYING D1	1	SEALED TAB HOUSING 4 POS. J.P.T.	PBT 20% GF	BROWN
185001-3 KEYING C1	1	SEALED TAB HOUSING 4 POS. J.P.T.	PBT 20% GF	BLUE
185001-2 KEYING B1	1	SEALED TAB HOUSING 4 POS. J.P.T.	PBT 20% GF	GREY
185001-1 KEYING A1	1	SEALED TAB HOUSING 4 POS. J.P.T.	PBT 20% GF	BLACK
REFERENCE TE	Qty	DESCRIPTION	MATERIAL	COLOR

REVISIONS					
F	LTR	DESCRIPTION	DATE	DWN	APVD
REV		MODIFICATIONS		DES	APP
	A	KEYING DIMENSION	19DEC94	JLQ	—
	B	ADDED NOTE △	DEC-96	JL	—
	C	ENGLISH TRANSLATION	18-MAR-98	—	—
	D	UPDATED NOTE △	12MAY16	KCD	SA



THIS DRAWING IS A CONTROLLED DOCUMENT. CE SCHÉMA EST UN DOCUMENT CONTRÔLÉ		DWN/DESSINE T. CORRIEU 08-APR-98	TE Connectivity	
DIMENSIONS: mm		CHK/VERIFIE J. LALANGE 08-APR-98	NAME TITRE	
TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERANCES NON SPECIFIEES SUIV NB DE DECIMALES: 1. DECIMALE ± 0.3 2. DECIMALES ± 0.1 3. DECIMALES ± 0.05 4. DECIMALES ± 0.025 ANGLES FINITION ± 5°		APVD/APPROUVE J. LALANGE 08-APR-98	PRODUCT SPEC SPEC PRODUIT 108-15103	
MATERIAL MATIERE SEE TABLE		APPLICATION SPEC SPEC APPLICATION —	SIZE FORMAT A1	
WEIGHT MASSE APPROX. 4.8		DRAWING NO N° D'IN	RESTRICTED TO RESERVE A	
CUSTOMER DRAWING/PLAN CLIENT		UNIDUMENT POUR REFERENCE	SCALE ECHELLE 3:1	
SHEET FEUILLE 1		OF DE 1	REV D	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[185001-6](#)