





- ① GLASS FILLED POLYESTER, BLACK
- ② PHOSPHOR BRONZE
- ③ CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101
PERFORMANCE LEVEL 2.
- ④ DATUMS ESTABLISHED BY CUSTOMER.
- ⑤ DRILLED HOLE DIAMETER 0.700 ± 0.025
COPPER THK $0.025 - 0.05$
TIN THICKNESS $0.004 - 0.01$
- ⑥ DIMENSION ESTABLISHED BY CUSTOMER.
- ⑦ GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): $1.27 \mu\text{m}$ MIN NICKEL AND ACTION
PIN: $0.5 \mu\text{m}$ MIN TIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.

THIS DRAWING IS THE PROPERTY OF TYCO ELECTRONICS. IT IS TO BE USED FOR THE MANUFACTURE OF THE PRODUCT SPECIFICALLY IDENTIFIED HEREON. IT IS TO BE KEPT IN THE FILES OF THE MANUFACTURER AND IS NOT TO BE REPRODUCED OR COPIED IN ANY MANNER WITHOUT THE WRITTEN PERMISSION OF TYCO ELECTRONICS. IT IS TO BE DESTROYED WHEN THE PRODUCT IS NO LONGER IN PRODUCTION.				OWN D. CARRO 01JUN05 CHK G. SKIPPER 01JUN05 APP G. SKIPPER 01JUN05		tyco Electronics		Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY, SIGNAL/GROUND COMBINATION, 72 POSITION, LEFT HAND, Z-PACK 12 HM		SIZE CASE CODE DRAWING NO A 00779 C=5120640		RESTRICTED TO	
mm		0 PLC ±. 2 PLC ±.013 1 PLC ±. 1 PLC ±. ANGLES ±.							
		FINISH							
MATERIAL HOUSING: 		CONTACTS:  							
CONTACTS: 		WEIGHT -		CUSTOMER DRAWING		SCALE 5:1 SHEET 1 OF 1 REV A			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5120640-1](#)