


DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION .19
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

PROD		LOC	DIST	REVISIONS				DATE		APPO
4092	DF	SO	P	F	ZONE	LTR	DESCRIPTION			
CODE						D	REV & REDWN PER DF-1137, DF-0697 TW	11-28-88		W.A.



- 1 MARKED PER AMP SPEC. MIL-STD-130
2 TO MATE WITH AMP LGH-IL RECEPTACLE WITH 1.69 BARREL DEPTH.

OBSOLETE	#10	15.50	865515-4
OBSOLETE	5/16	11.00	865515-3
OBSOLETE	5/16	15.50	865515-2
	1/4	8.50	865515-1
	B	A	PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± .02 3 PLC DEC ± .010 ANGLES ± -		DR 11-29-88 T. WIEST	AMP AMP INCORPORATED Harrisburg, Pa. 17105	
CHK <i>M. Gardner</i> 12-9-88		APPR <i>M. Gardner</i> 12-9-88	NAME	
MATERIAL -		APPD -	LGH-IL POSITIVE STOP LEAD ASS'Y WITH RING TONGUE TERM.	
FINISH -		PRODUCT SPEC -	SIZE C FSCM NO 00779 DRAWING NO 865515	
WEIGHT -		APPLICATION SPEC -	SCALE 2:1 SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[865515-1](#)