


REVISIONS			
REV	ECR NO	DESCRIPTION	DATE
A	23737	NEW RELEASE	08/19/04



NOTES:

- 1- ALL DIMENSIONS ARE IN INCHES
- 2- FILAMENT SHAPE MUST BE UNIFORM, WITH COILS EVENLY SPACED AND FREE OF TWIST OR SHORTING
- 3- LAMPS SHALL BE CLEAN WITH NO FOREIGN MATERIALS OR GLASS CHIPS INSIDE
- 4- LAMP ENVELOPE SHALL BE CLEAR AND FREE OF BUBBLES, SCRATCHES, OR DISCOLORATION
- 5- CLEAR GLASS PROPERLY ANNEALED, SHALL BE UNIFORM IN SHAPE AND SUBSTANTIALLY FREE OF PRISMATIC ACTION
- 6- LAMPS SHALL BE CAPABLE OF OPERATION AND STORAGE FROM -65° TO 80°C WITHOUT DEGRADATION
- 7- LAMPS SHALL BE PROPERLY PACKAGED IN CONTAINERS SUITABLE TO PREVENT ANY DAMAGE DURING SHIPMENT
- 8- MFR'S IDENTIFICATION AND BULB NUMBER TO APPEAR ON THE GLASS WITHIN THIS LENGTH
- 9- BULBS MUST COMPLY WITH SAE/USCAR-3
- 10- PARTS TO BE LEAD FREE.

CML PART NO.	192HLF
DESIGN VOLTAGE	13.0
DESIGN AMPS	0.33 ± 10%
CANDLE POWER (APPROX.)	3.0 ± .20%
RATED LIFE HOURS	1000
FILAMENT SHAPE	C-2V

SDRC FILE NAME: B18566

DIM ARE IN INCHES

Q FOR INSPECTION USE ONLY
X SPC DOCUMENTATION REQ. (X R CHARTS)

THIS DWG IS THE PROPERTY OF CHICAGO MINIATURE LAMP, INC. AND IS PROPRIETARY IN GENERAL AND IN DETAIL. IT SHALL NOT BE COPIED OR ITS CONTENTS REVEALED TO OUTSIDE PARTIES WITHOUT THE WRITTEN CONSENT OF CHICAGO MINIATURE LAMP, INC.

DRAWN BY
RHW
CHECKED BY
RHW
ENG. APPR.
RHW
UNLESS OTHERWISE SPECIFIED TOLERANCES ON:
+/- .015
ANGLE +/- 5 DEG.

DATE
8/19/04
DATE
8/20/04
DATE
8/20/04
MATERIAL
FINISH


PART NO
192HLF

MODEL NO

MOLD NO

MATERIAL

FINISH



CHICAGO MINIATURE LAMP, INC.
147 CENTRAL AVE. HACKENSACK, NJ 07601

TITLE
T-3 1/4
WEDGE BASE LAMP

DIST. V/S
DWG NO
B18566

REV
A

SCALE
3:1
SHEET

ORIGINAL
WHEN RED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

VCC:
192HLF