

PCB LAYOUT - COMPONENT VIEW
RECOMMENDED PCB THICKNESS : 1.6 mm

TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR: PBT
FLAMMABILITY RATING: UL94-V0
COLOR: WHITE
CONTACT MATERIAL: BRASS
CONTACT PLATING: GOLD OVER Ni
COVER MATERIAL: BRASS
COVER PLATING: Ni
QUALITY CLASS: 1 500 MATING CYCLES

ENVIRONMENTAL
OPERATING TEMPERATURE: -40°C UP TO +85°C
COMPLIANCE: LEAD FREE & ROHS





ELECTRICAL
CURRENT RATING:
- PIN 1 & PIN 4: 3 A
- OTHER PINS: 1 A
WORKING VOLTAGE: 30 VAC MAX
WITHSTANDING VOLTAGE: 500 VAC/MIN
INSULATION RESISTANCE: > 1000 MΩ
CONTACT RESISTANCE: 30 mΩ MAX

MECHANICAL
INSERTION FORCE: 35.0N MAX
EXTRACTION FORCE: 10.0N MIN


STANDARD
 CERTIFIED: E323964

SOLDERING
JEDEC LEAD FREE WAVE SOLDERING PROCESS

PACKAGING
TRAY



RoHS Compliant								
G				PROJECTION: 	GENERAL TOLERANCE	 WÜRTH ELEKTRONIK		
F					.X = $\pm$ 0.2			
E					.XX = $\pm$ 0.15			
D								
C	20-JUN-17	OTHER PINS	AK	APPROVAL: NPr	UNIT: MM	DESCRIPTION: USB 2.0 TYPE A HORIZONTAL THT		SIZE A4
B	23-JAN-17	CERTIFIED	AK		SCALE:			
A	19-JUN-15	PDF	AK		SHEET: 1/3	WERI PART NO: 614 004 190 021		
REV	DATE	FILE	BY		DRAW: AK			



RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = ± 0.2 .XX = ± 0.15	 WÜRTH ELEKTRONIK	
G							
F							
E							
D				APPROVAL: NPr	UNIT: MM	DESCRIPTION: USB 2.0 TYPE A HORIZONTAL THT	
C					SCALE:		
B					SHEET: 2/3		
A					DRAW: AK		
REV	DATE	FILE	BY			WERI PART NO: 614 004 190 021	SIZE A4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Electronics:](#)

[614004190021](#)