

Product: [9264](#) 



Audio & Instrumentation, 24 AWG Stranded TC, O/A Foil, CM PVC Jacket

Product Description

Audio & Instrumentation, 24 AWG Uni-strand (7x32) tinned copper conductor, flame-retardant polypropylene insulation, Beldfoil® shield (100% coverage), CM PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
24	7x32	TC - Tinned Copper	0.024 in	1

Conductor Count:	1
------------------	---

Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PP - Polypropylene	0.078 in	0.027 in

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	24	7x32

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	.122 x .146 in	0.02 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
23.6 Ohm/1000ft	20 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
30 pF/ft

Inductance

Nominal Inductance
0.85 µH/ft

Impedance

Nominal Characteristic Impedance
50 Ohm

Delay

Nominal Delay
1.64 ns/ft

Current

Max. Recommended Current [A]
2.2 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V RMS (UL AWM Style 1770)

Temperature Range

UL Temp Rating:	80°C (UL AWM Style 1770)
Operating Temp Range:	-30°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	12 lbs/1000ft
Max. Pull Tension:	94 lbs
Min Bend Radius (Overall):	1.5 in

Standards

UL AWM Style Compliance:	UL Style 1770 (300 V 80°C)
RG Type:	N/A

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-10-13
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LS0H, Toxicity Testing

UL Flammability:	VW-1
UL voltage rating:	300 V RMS (UL AWM Style 1770)

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
9264 0101000	Black	Reel	1,000 ft	612825358763

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Product Notes

Notes:	Tear-drop, machine strippable coaxial cable.
--------	--

History

Update and Revision:	Revision Number: 0.266 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9264 0101000](#)