




Bestückungsplan / contact layout



■ bestückt / assemble

Leiterplatten-Lochbild / PCB drillhole pattern



Tauchlötanschluss 0,64 x 0,64 mm / solder terminal 0,64 x 0,64 mm

Isolierwerkstoff / housing material : LCP GF30

Bauart 2 / type 2

Anforderungsstufe 1 = 500 Steckzyklen / performance class 1 = 500 mating cycles

Fehlende Maße und Angaben gemäß IEC 60 603-2 / DIN EN 60 603-2

Missing information and dimensions according to IEC 60 603-2

Information:		Tolerances	All Dimensions in mm	Scale	2:1
All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		Subject to modification without prior notice. Drawing will not be updated.		Designation	
				Federleiste H 11 Löt Fem. Connector H 11 Solder	
c	14.12.2010	www.ERNI.com		424654	
Index	Date	V:00070327.SZA		STVH11	

Consider protection memo from DIN 34

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[424654](#)