


DASH NO.	APPLICATION		REVISIONS			
	NEXT ASSY.	USED ON	LTR	ECO#	DESCRIPTION	DATE
	n/a	HS35	H	9661	ADD -512, -551 & -591 DASH NO.	11/30/15



DASH NO.	BORE $\pm \frac{.002}{.000}$	GO GAGE	NO-GO GAGE	REF ONLY
-500	0.500	0.5000 (-)	0.5020 (-)	1/2 in.
-512	0.5125	0.5125 (-)	0.5145 (-)	13 mm
-551	0.552	0.5520 (-)	0.5540 (-)	14 mm
-591	0.591	0.5910 (-)	0.5930 (-)	15 mm
-625	0.625	0.6250 (-)	0.6270 (-)	5/8 in.
-630	0.631	0.6310 (-)	0.6330 (-)	16 mm
-709	0.7085	0.7085 (-)	0.7105 (-)	18 mm
-750	0.750	0.7500 (-)	0.7520 (-)	3/4 in.
-789	0.788	0.7880 (-)	0.7900 (-)	20 mm

NOTES:

- MATERIAL: PHILLIPS RYTON R4, BLACK, VIRGIN. ALT. MATERIAL: DELRIN 150
- INSIDE RADIUS, .015 MIN.
- GO/NO-GO GAGE PIN SIZES FOR INSPECTION REFERENCE
- THIS FEATURE APPLIES TO -500, -521, -551 AND -591.
- MUST INSPECT BORE SIZE PER 08202-001 PROCEDURE.
- OTHER DASH NUMBERS ARE ON SEPARATE DRAWINGS
- MAY BE MADE FROM 32044-TAB PART BY MACHINING THESE FEATURES ONLY. OTHERWISE COUNTERBORE FEATURE NOT REQUIRED.

MATERIAL/FINISH: See Notes	APPROVALS DRAWN KRB	DATE 02/07/07
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES, APPLY AND APPLY AFTER FINISH .XX ±.01 .XXX ±.005 ANGLES ±0° 30' ALL DIA. TO BE $\odot$ WITHIN .010	APPR	
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE IF EXPORTED FROM THE UNITED STATES MUST BE IN ACCORDANCE WITH THE BUREAU OF INDUSTRY, EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.		
THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF BEI SENSORS. ANY REPRODUCTION, USE OR DISCLOSURE OF THIS DOCUMENT WITHOUT WRITTEN CONSENT OF BEI SENSORS IS EXPRESSLY PROHIBITED.		

**BEI SENSORS**

7230 Hollister Ave.  
Goleta, Ca 93117-2891  
Tel: (805) 968-0782  
Fax: (805) 968-3154

TITLE BUSHING, INSULATOR, THRU  
HS35

SIZE A	CAGE CODE 1RB90	DWG NO. 32043-TAB	REV. H
SCALE: NONE		FILE: 32043-TAB_H	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Sensata:](#)

[32043-500](#) [32043-625](#) [32043-750](#)