

CHERRY MW 2900



Models may vary from the image shown

Industrial, medical and commercial Nema 4 rated optical mouse with scrolling buttons

Interface:

- USB

Product Approvals:

- CE
- FCC
- RoHS



Dimensions (product):

63.56 mm x 126.93 mm x 40.37 mm / 2.50 x 4.97 x 1.59 in

Reliability:

- MTBF > 20,000 hours

Mouse:

- Number of Keys: 5
- Mouse Wheel Design: 3 scroll buttons design allows for quick and easy navigation while eliminating bacterial and dirt traps
- Design: Symmetrical
- Connection: USB

Packaging Unit:

- Number of products in the master package: 24
- Number of master packages per pallet: 36

Warranty:

1 year

Errors, technical changes and delivery delays may occur. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Key Benefits

- Rugged and fully sealed:
Compact easy-to-wipe casing,
Completely sealed silicone-based casing-NEMA 4 rated,
Suitable for rinsing with cleaning and disinfection fluids.
Impervious to typical hospital cleaning solutions.
Impervious to liquid, sand and dust,
No room for bacterial and infection traps,
Hypo-allergenic, silicone skin provides a soft feel
- Humidity: 5% to 100%

Technical Data:

Housing Color:

black

Key Color:

black

Weight (product):

approx. 148.15 g / approx. 0.33 lb

Total Weight (with packaging):

approx. 179.2 g / approx. 0.40 lb

Cable Length:

4.5 ft

Storage Temperature:

-30°C to 85°C / -22°F to +185°F

Operating Temperature:

0°C to 70°C / 32°F to +158°F

Models:

(possible country/layout versions, others available on request)

	Product Name	Order Number
1	CHERRY MW 2900	MW-2900-2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CHERRY:](#)

[MW-2900-2](#)