



SPECIFICATIONS


- 1. CASE:
22 GA. (.030) CRS, TIN PLATED
- 2. RATED CURRENT:
20A
- 3. RATED VOLTAGE:
50VDC
- 4. TEST VOLTAGE:
LINE TO GROUND: 150VDC



INSERTION LOSS (50Ω TYPICAL)

	.02 MHz	.15 MHz	.50 MHz	1.5 MHz	5.0 MHz	50 MHz
L/L	35 db	55 db	65 db	65 db	65 db	60 db
L/G	30 db	50 db	60 db	60 db	60 db	50 db

SCHEMATIC



NEXT ASSY	USED ON
APPLICATION	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ±.030 ± .XXX ±.010	CONTRACT NO.		FILTER CONCEPTS INC.		
	APPROVALS	DATE			
	DRAWN GIANG TRINH	10-02-03	APPLICATION DRAWING D2L20 FS01 FILTER		
	CHECKED DANNIEL VUONG	10-02-03			
	MATERIAL		SIZE B	CODE IDENT NO.	DRAWING NO. 7004-1
FINISH			SCALE 2/3		SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Astrodyne TDI:](#)

[D2L20 FS01](#)