

## Dual-Port USB Car Charger for Tablets and Cell Phones with Quick Charge 2.0 Technology

MODEL NUMBER: **U280-C02-S-M6**



Built-in USB Micro-B cable with Quick Charge 2.0 and auto-sensing USB-A port allow you to charge 2 mobile devices, such as a tablet and cell phone, in your vehicle at the same time. Quick Charge 2.0 delivers up to 75% faster charging vs. conventional USB charging.

### Description

The U280-C02-S-M6 Dual USB Car Charger lets you quickly and safely charge two USB-powered mobile devices in your vehicle at the same time. You and your passenger can connect your cell phones simultaneously to ensure full charges when you reach your destination.

Also ideal for tablets, MP3 players and other USB devices, the U280-C02-S-M6 features a built-in six-foot USB Micro-B cable with Quick Charge 2.0 technology for rapid charging of compliant devices. Available outputs include 5V 2A, 9V 1.67A and 12V 1.25A. The cable's auto-sensing technology allows it to also charge devices without Quick Charge capability at a maximum power output of 5V 2.4A. The specially coiled cable takes up much less space than a regular six-foot cable.

The U280-C02-S-M6's USB port also features auto-sensing technology that detects the connected device and automatically adjusts to the appropriate power level up to 5V 2.4A, perfect for fast-charging tablets and e-readers. It's also compatible with both Apple and Android, as well as other platforms.

This ultra-compact charger works with any standard 12V DC vehicle power outlet. A front-facing LED indicates successful charging.

### Features

#### Charge 2 Mobile Devices in Your Vehicle at the Same Time

- Ideal for cell phones, tablets, e-readers and MP3 players
- Auto-sensing USB port detects connected device and adjusts to proper power level up to 5V 2.4A
- Compatible with Apple, Android and other platforms
- Works with any standard 12V DC vehicle power outlet
- LED indicates successful charging

#### Built-In USB Micro-B Cable with Quick Charge 2.0

- Quick Charge 2.0 Class A 5/9/12V technology
- Quick Charge 2.0 delivers up to 75% faster charging vs. conventional USB charging.
- Also charges non-QC devices at maximum power output of 5V 2.4A
- Coiled to take up less space than regular 6 ft. cable

### Highlights

- Quick Charge 2.0 Class A 5/9/12V technology
- USB Micro-B cable with Quick Charge provides optimal charging for compatible devices
- Ideal for cell phones, tablets, e-readers and MP3 players
- Auto-sensing USB-A port provides power output up to 5V 2.4A
- Works with any standard 12V DC vehicle power outlet
- Compatible with Apple, Android and other platforms

### Package Includes

- U280-C02-S-M6 Dual USB Car Charger for Tablets and Cell Phones with Quick Charge 2.0 Technology, 6 ft.



Powering Business Worldwide



## Specifications

| OVERVIEW                           |                                                             |
|------------------------------------|-------------------------------------------------------------|
| UPC Code                           | 037332196309                                                |
| Product Type                       | Car Charger                                                 |
| Charging Form Factor               | Direct Plug-In                                              |
| Device Compatibility               | Phone; Tablet; Amazon Kindle                                |
| INPUT                              |                                                             |
| Nominal Input Voltage(s) Supported | 12V DC                                                      |
| Input Plug Type                    | Car Auxiliary Power Outlet                                  |
| OUTPUT                             |                                                             |
| Overload Protection                | Yes                                                         |
| CONNECTIONS                        |                                                             |
| Number of Ports                    | 1                                                           |
| Side A - Connector 1               | Car Cigarette Lighter                                       |
| Side B - Connector 1               | USB A (FEMALE)                                              |
| Side B - Connector 2               | MICRO-USB B (MALE)                                          |
| CHARGING                           |                                                             |
| Number of Charging Ports           | 1                                                           |
| Total Charging Amps                | 3.65A                                                       |
| Total Charging Watts               | 27                                                          |
| Charging Method                    | USB                                                         |
| Charging Method Detail             | Quick Charge 2.0                                            |
| Charging Port Type                 | USB A (FEMALE)                                              |
| Charging Ports Details             | USB-A: 5V/2.4A (12W)USB Micro-B: 5V/2A, 9V/1.67A, 12V/1.25A |
| Charging Ports / Amps              | (1) 2.4A; (1) 2A / 1.67A / 1.25A                            |
| PHYSICAL                           |                                                             |
| Color                              | White                                                       |
| Shipping Dimensions (hwd / in.)    | 0.50 x 7.80 x 6.70                                          |
| Shipping Dimensions (hwd / cm)     | 1.27 x 19.81 x 17.02                                        |
| Shipping Weight (lbs.)             | 0.10                                                        |
| Shipping Weight (kg)               | 0.05                                                        |



Powering Business Worldwide



| ENVIRONMENTAL                       |                                     |
|-------------------------------------|-------------------------------------|
| Operating Temperature Range         | 32° to 104°F (0° to 40°C)           |
| Storage Temperature Range           | -4° to 140°F (-20° to 60°C)         |
| Relative Humidity                   | 30% to 90% RH, Non-Condensing       |
| FEATURES & SPECIFICATIONS           |                                     |
| GaN Technology                      | No                                  |
| Overcurrent Protection              | Yes                                 |
| Overvoltage Protection              | Yes                                 |
| Quick Charge Compliant              | 2.0                                 |
| STANDARDS & COMPLIANCE              |                                     |
| Product Compliance                  | RoHS; CE (Europe); REACH; FCC (USA) |
| WARRANTY & SUPPORT                  |                                     |
| Product Warranty Period (Worldwide) | 2-year limited warranty             |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U280-C02-S-M6](#)