



Representative Image

Catalog No. 1SNA645062R0700

Description: OBOA1000-115VUC Optocoupler R600 A1-A2=115VAC/DC,24-400VAC/25 mA-1 A, Triac

UPC No 4013614508127

Home > Controls & Protective Relays > Interface Relays & Optocouplers

Descriptors

Category	Interface Relays & Optocouplers
----------	---------------------------------

Specifications

Function	Boxed optocoupler R600
Rated Control Supply Voltage	115 V AC / DC
Output Signal	24 ... 400VAC / 25 mA ... 1 A
Terminal Type	Screw Terminals
Output	solid-state output
Contact material	Triac
Product Main Type	R600
RoHS Status	Following EU Directive 2011/65/EU
Object Classification Code	K

Classifications

ETIM 4	EC001504 - Optocoupler
ETIM 5.0	EC001504 - Optocoupler
ETIM 6.0	EC001504 - Optocoupler
ETIM 7	EC001504 - Optocoupler
eClass	7.0 27371604

Dimensions

Product Net Width	6 mm
Product Net Height	67.5 mm
Product Net Depth / Length	70 mm
Product Net Weight	0.02kg

Package Information

Package Level 1 Units	10 piece
Package Level 1 Width	73 mm

by ABB

Package Information

Package Level 1 Height	71 mm
Package Level 1 Depth / Length	80 mm
Package Level 1 Gross Weight	0.23 kg
Package Level 1 EAN	3472596450625

Ordering

Minimum Order Quantity	10
Customs Tariff Number	85369095
ECCN	N
ECN	N
ABB MDF Code	3DL - Relays (LV / Control + Protection)
ABB Business Unit	ELSP - Smart Power