



### Catalog No. 9T51B0013G03

Description: "1C,3kVA,240x480-120/240,100C,3R,ES,QB"

UPC No 783173806999

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

#### Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T5

#### Specifications

Phase	1
PriVoltage	240x480
SecVoltage	120/240
KVA	3.0 KVA
Coil Material	CU
TempRise	100.0 °C
ElecShield	Y
Sub Type	Standard
Frequency	60 Hz
FrameSize	14350
Net Weight	55
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
EnergyEfficiency	None
KFactor	K1
Enclosure Type	NEMA 3R
Net Weight	55
Sound	Std
GSA Compliance	Yes

#### Classifications

UL	Yes
cUL	Yes
CE	No

## Dimensions

Width	9.4 in
Depth	6.7 in
Height	11.1 in