



Catalog No. 9T51B0032

Description: "1C,2kVA,120x240-120/240,100C,3R,QB"

UPC No 783173008409

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

| | |
|-------------|---|
| Category | Single-Phase: .050kVA-3kVA and 5kVA-25kVA |
| GO Schedule | T5 |

Specifications

| | |
|------------------|----------|
| Phase | 1 |
| PriVoltage | 120x240 |
| SecVoltage | 120/240 |
| KVA | 2.0 KVA |
| Coil Material | CU |
| TempRise | 100.0 °C |
| ElecShield | N |
| Sub Type | Standard |
| Frequency | 60 Hz |
| FrameSize | 14250 |
| Net Weight | 45 |
| TempClass | 180.0 °C |
| AmbTemp | 40.0 °C |
| InsulSys | IS-12 |
| EnergyEfficiency | None |
| KFactor | K1 |
| Enclosure Type | NEMA 3R |
| Net Weight | 45 |
| Sound | Std |
| GSA Compliance | Yes |

Classifications

| | |
|-----|-----|
| UL | Yes |
| cUL | Yes |
| CE | No |

Dimensions

| | |
|--------|---------|
| Width | 9.4 in |
| Depth | 6.7 in |
| Height | 11.1 in |