

Omron's Easy-To-Use Programmable Relay Offers Precision and Space Savings for Small Scale Control Applications

zen

Smart. Simple. Small.

The ideal solution for managing a wide range of simple applications, including automatic lighting, access control, conveyor positioning, pump control, testing equipment, watering systems, or ventilation systems.



ZEN Starter Kits – Great introduction to the power and simplicity of the ZEN Series

Includes everything for self-training, system design, and installation:

- 10 I/O CPU
- PC programming cable (RS-232 to ZEN)
- Support software
- Manuals
- Simulator switches



ZEN-STARTER01-V2	AC I/O Kit with ZEN-10C1AR-A-V2	\$193.00
ZEN-STARTER02-V2	DC I/O Kit with ZEN-10C1AR-D-V2	\$193.00

System Advantages

- Delivers the flexibility and functionality of separate timers, counters, and relays for control applications with up to 44 I/O.
- New economy CPU models – **perfect for applications that require less than 10 or 20 points of I/O.** (Does not accept expansion units).
- Save time by using the memory cassette to transfer programs between ZEN units and standardize updates to end users.
- Reduce wiring and engineering time using simple ladder logic programming with the push of a button or click of the mouse.
- Easily add up to 3 ultra-slim 35mm, 8 I/O expansion units when more points of control are required.

System Features

- Accurate analog inputs $\pm 1.5\%$ FS.
- Wide supply voltage range of 10.8 to 28.8 VDC.
- Flexible mounting – either horizontal or vertical.
- New CPUs with built-in RS-485 communications for data sharing.
- Advanced high-value counting with 8-digit counter and 8-digit comparators, in addition to 16 standard counters.
- One 150-Hz high-speed counter available on models with DC power supply.
- Twin-timer operation allows you to set ON and OFF times separately, greatly simplifying intermittent operation.
- Password function ensures security.
- Display user-set messages or analog-converted values.

ZEN Support Software

- Easily write ladder programs, monitor programs online, set parameters, print, and save files in the Windows® environment.
- Offers simulation capability to simplify program debugging; allows programs to be simulated on a personal computer without connecting to ZEN.



Smart. Simple. Small.

10-Point CPU Programmable Relay Units

Appearance	Description	Inputs / Power Supply	Outputs	Analog Input / Comparators	8-digit Counter / Comparators	Model Number	List Price
 90 H x 70 W x 56 D mm	10 I/O CPU Expandable up to 34 I/O	6 100 to 240 VAC 12 to 24 VDC	4 Relays	-	Yes / 4	ZEN-10C1AR-A-V2	\$115.00
				2 Ch. 0 - 10V / 4	Yes / 4	ZEN-10C1DR-D-V2	\$115.00
	10 I/O CPU Economy model (non-expandable)	100 to 240 VAC 12 to 24 VDC	4 Relays	2 Ch. 0 - 10V / 4	Yes / 4	ZEN-10C1DT-D-V2	\$115.00
				-	Yes / 4	ZEN-10C3AR-A-V2	\$90.00
	9 I/O CPU with RS-485 Communications Expandable up to 33 I/O	100 to 240 VAC 12 to 24 VDC	3	2 Ch. 0 - 10V / 4	Yes / 4	ZEN-10C3DR-D-V2	\$90.00
				-	Yes / 4	ZEN-10C4AR-A-V2	\$185.00
			2 Ch. 0 - 10V / 4	Yes / 4	ZEN-10C4DR-D-V2	\$185.00	

20-Point CPU Programmable Relay Units

Appearance	Description	Inputs / Power Supply	Outputs	Analog Input / Comparators	8-digit Counter / Comparators	Model Number	List Price
 90 H x 122.5 W x 56 D mm	20 I/O CPU Expandable up to 44 I/O	12 100 to 240 VAC 12 to 24 VDC	8 Relays	-	Yes / 4	ZEN-20C1AR-A-V2	\$155.00
				2 Ch. 0 - 10V / 4	Yes / 4	ZEN-20C1DR-D-V2	\$155.00
	20 I/O CPU Economy model (non-expandable)	100 to 240 VAC 12 to 24 VDC	8 Relays	2 Ch. 0 - 10V / 4	Yes / 4	ZEN-20C1DT-D-V2	\$155.00
				-	Yes / 4	ZEN-20C3AR-A-V2	\$130.00
				2 Ch. 0 - 10V / 4	Yes / 4	ZEN-20C3DR-D-V2	\$130.00

10 and 20 I/O models available without display. Please refer to datasheet for more information.

I/O Expansion Units

Appearance	Description	Inputs / Power Supply	Outputs	Model Number	List Price
 90 H x 35 W x 56 D mm	8 I/O Expansion units	4 100 to 240 VAC 12 to 24 VDC	4 Relays	ZEN-8E1AR	\$69.52
				ZEN-8E1DR	\$69.52
			Transistors	ZEN-8E1DT	\$69.52

ZEN Accessories

Appearance	Description	Model Number	List Price
	ZEN Support Software	ZEN-SOFT01V4	\$40.00
	ZEN Programming Cable – Serial to ZEN (2m)	ZEN-CIF01	\$80.08
	Memory Cassette EEPROM – Copies program to multiple units	ZEN-ME01	\$31.25
	ZEN Battery – Use with controller CPU to provide 10 years of memory protection to prevent data loss in the event of an extended power outage (45 H x 17.5 W x 44 D mm)	ZEN-BAT01	\$37.33



OMRON ELECTRONICS LLC
800.556.6766
www.omron247.com

OMRON CANADA
416.286.6465
www.omron.ca

MEXICO SALES OFFICES

Mexico, D.F. (52) 555 660 31 44 Monterrey, N.L. (52) 818 377 42 81
Ciudad Juárez, Chih (52) 656 623 70 83 Mexicali, B.C. (52) 1 686 838 01 15

OTHER LATIN AMERICAN SALES

(56) 2206 4592 mela@omron.com

ARGENTINA SALES OFFICE

Cono Sur (54) 11 4787 1129

BRAZIL SALES OFFICE

Sao Paulo (55) 11 2101 6300 www.omron.com.br

CHILE SALES OFFICE

Santiago (56) 2206 4592

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Omron:

[ZEN-STARTER01-V2](#)