

Order Code	L (mm)	Tlo (mm)	Tli (mm)	Thread Size	Wrench Size
971050244	5	5,0	3,0	M 2.0	SW 4
971070244	7	8,0	3,0	M 2.0	SW 4
971080244	8	6,0	6,0	M 2.0	SW 4
971100244	10	5,0	5,0	M 2.0	SW 4
971130244	13	5,0	6,0	M 2.0	SW 4
971140244	14	5,0	6,0	M 2.0	SW 4
971150244	15	6,0	6,0	M 2.0	SW 4
971200244	20	5,0	7,0	M 2.0	SW 4
971250244	25	5,0	7,0	M 2.0	SW 4
971300244	30	5,0	6,0	M 2.0	SW 4
971050154	5	6,0	3,0	M 2.5	SW 5
971060154	6	6,0	2,5	M 2.5	SW 5
971070154	7	6,0	4,0	M 2.5	SW 5
971080154	8	6,0	5,0	M 2.5	SW 5
971090154	9	6,0	5,0	M 2.5	SW 5
971100154	10	6,0	5,0	M 2.5	SW 5
971110154	11	6,0	6,0	M 2.5	SW 5
971120154	12	6,0	7,0	M 2.5	SW 5
971150154	15	6,0	6,0	M 2.5	SW 5
971200154	20	6,0	10,0	M 2.5	SW 5
971250154	25	6,0	10,0	M 2.5	SW 5
971300154	30	6,0	10,0	M 2.5	SW 5
971050354	5	8,0	3,0	M 3.0	SW 5
971060354	6	8,0	3,0	M 3.0	SW 5
971070354	7	8,0	4,0	M 3.0	SW 5
971080354	8	8,0	5,0	M 3.0	SW 5
971100354	10	8,0	5,0	M 3.0	SW 5
971110354	11	8,0	5,0	M 3.0	SW 5
971120354	12	8,0	8,0	M 3.0	SW 5
971140354	14	8,0	7,0	M 3.0	SW 5
971150354	15	8,0	8,0	M 3.0	SW 5
971160354	16	8,0	10,0	M 3.0	SW 5
971180354	18	8,0	8,0	M 3.0	SW 5
971200354	20	8,0	10,0	M 3.0	SW 5
971250354	25	8,0	10,0	M 3.0	SW 5
971270354	27	8,0	10,0	M 3.0	SW 5
971280354	28	10,0	10,0	M 3.0	SW 5
971300354	30	10,0	10,0	M 3.0	SW 5
971350354	35	8,0	10,0	M 3.0	SW 5

Surface coating: nickel-plated

Würth Elektronik eiSos GmbH & Co. KG
EMC & Inductive Solutions

Max-Eyth-Str. 1
74638 Waldenburg
Germany
Tel. +49 79 42 945 - 0

www.we-online.com
eiSos@we-online.com



CREATED
D. Fandrey

CHECKED
S. Klingler

PROJECTION
METHOD

SCALE
5 : 1

DESCRIPTION

AsSBRIE
Brass Spacer Stud Metric
Thread int./ext.

MATERIAL
CuZn39Pb3






GENERAL TOLERANCE
DIN ISO 2768 T1m

ORDER CODE
971xxxxx4

WEIGHT STATUS
Released

REV DATE
1.0 2014-10-01

PAGE
DE 1 / 1



Order Code	L (mm)	Tlo (mm)	Tli (mm)	Thread Size	Wrench Size
971050324	5	6,0	2,5	M 3.0	SW 5.5
971060324	6	6,0	3,0	M 3.0	SW 5.5
971070324	7	8,0	4,0	M 3.0	SW 5.5
971080324	8	6,0	5,0	M 3.0	SW 5.5
971090324	9	8,0	5,0	M 3.0	SW 5.5
971100324	10	6,0	5,0	M 3.0	SW 5.5
971120324	12	6,0	6,0	M 3.0	SW 5.5
971130324	13	8,0	8,0	M 3.0	SW 5.5
971140324	14	8,0	8,0	M 3.0	SW 5.5
971150324	15	6,0	8,0	M 3.0	SW 5.5
971160324	16	6,0	10,0	M 3.0	SW 5.5
971170324	17	8,0	10,0	M 3.0	SW 5.5
971180324	18	8,0	10,0	M 3.0	SW 5.5
971190324	19	6,0	10,0	M 3.0	SW 5.5
971200324	20	8,0	10,0	M 3.0	SW 5.5
971210324	21	8,0	10,0	M 3.0	SW 5.5
971220324	22	8,0	10,0	M 3.0	SW 5.5
971250324	25	8,0	10,0	M 3.0	SW 5.5
971280324	28	6,0	10,0	M 3.0	SW 5.5
971290324	29	8,0	10,0	M 3.0	SW 5.5
971300324	30	6,0	10,0	M 3.0	SW 5.5
971350324	35	6,0	10,0	M 3.0	SW 5.5
971400324	40	6,0	10,0	M 3.0	SW 5.5
971450324	45	8,0	6,0	M 3.0	SW 5.5
971500324	50	6,0	10,0	M 3.0	SW 5.5
971600324	60	6,0	10,0	M 3.0	SW 5.5
971050474	5	8,0	3,0	M 4.0	SW 7
971060474	6	8,0	3,0	M 4.0	SW 7
971070474	7	8,0	3,0	M 4.0	SW 7
971075474	8	4,5	5,0	M 4.0	SW 7
971080474	8	8,0	4,0	M 4.0	SW 7
971100474	10	8,0	5,0	M 4.0	SW 7
971110474	11	4,6	6,0	M 4.0	SW 7
971120474	12	8,0	8,0	M 4.0	SW 7
971150474	15	8,0	10,0	M 4.0	SW 7
971160474	16	5,0	10,0	M 4.0	SW 7
971180474	18	8,0	10,0	M 4.0	SW 7
971200474	20	10,0	10,0	M 4.0	SW 7
971230474	23	8,0	10,0	M 4.0	SW 7
971250474	25	10,0	10,0	M 4.0	SW 7
971300474	30	10,0	10,0	M 4.0	SW 7
971350474	35	8,0	9,0	M 4.0	SW 7
971400474	40	10,0	10,0	M 4.0	SW 7
971100584	10	8,0	6,0	M 5.0	SW 8
971120584	12	7,0	8,0	M 5.0	SW 8
971150584	15	8,0	10,0	M 5.0	SW 8
971200584	20	8,0	10,0	M 5.0	SW 8
971250584	25	8,0	10,0	M 5.0	SW 8

Surface coating: nickel-plated

Würth Elektronik eiSos GmbH & Co. KG
EMC & Inductive Solutions

Max-Eyth-Str. 1
74638 Waldenburg
Germany
Tel. +49 79 42 945 - 0

www.we-online.com
eiSos@we-online.com



CREATED
D. Fandrey

CHECKED
S. Klingler

PROJECTION
METHOD SCALE
5 : 1

DESCRIPTION
AsSBRIE
Brass Spacer Stud Metric
Thread int./ext.

MATERIAL
CuZn39Pb3

GENERAL TOLERANCE
DIN ISO 2768 T1m

ORDER CODE
971xxxxx4

WEIGHT STATUS
Released

REV DATE
1.0 2014-10-01

PAGE
DE 1 / 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Electronics:](#)

[971250354](#)