



RVA-SWD-06M-C100

SWD cable of ST-LINK/ V2, 20-pin IDC to 6-pin wire-to -board connector

Rev.1.0
2022-03-10





1. REVISION RECORD

REV NO.	REV DATE	CONTENTS	REMARKS
1.0	2022-03-10	Initial Release	



2. CONTENTS

1. REVISION RECORD.....	2
2. CONTENTS.....	3
3. DRAWING.....	4
4. PIN ASSIGNMENT AND PIN CONNECTORS	5
4.1 Pin assignment.....	5
4.2 Pin connectors.....	5
5. WIRE SPECIFICATION	6
5.1 Electrical properties.....	6
5.2 Physical properties.....	6
6. LEGAL INFORMATION.....	7



4. PIN ASSIGNMENT AND PIN CONNECTORS

4.1 Pin assignment

Connector A	Pin Functionality	Connector B	Note
1	VCC_3.3V	1	Red
2	/		Cut flat
3	/		
4	/		
5	/		
6	/		
7	SW_DIO	4	Grey
8	GND	3	Grey
9	SW_CLK	2	Grey
10	/		Cut flat
11	/		
12	/		
13	SWO	6	Grey
14	/		Cut flat
15	RST	5	Grey
16	/		Cut flat
17	/		
18	/		
19	/		
20	/		

4.2 Pin connectors

Connector A: 2x10pins, 2.54mm pitch size, female, IDC socket

ITEM	DESCRIPTION
Pitch size	2.54mm
No. of pins	2x10
Single line max current	1.0Amp
Contact resistance	30m Ohm Max. at 6V DC0.3V
Insulation resistance	1000M Ohm Min at 500V DC
Dielectric voltage	500V AC /Minute

Connector B: 1X6 pins, 1.25mm pitch size, female, Molex connector

ITEM	DESCRIPTION
Pitch size	1.25mm
No. of pins	6
Flammability	94V-0
Glow-Wire Capable	No
Material - Resin	Polyester
Temperature Range - Operating	-40° C to +105°C



5. WIRE SPECIFICATION

5.1 Electrical properties

ITEM	DESCRIPTION
Voltage rating	300V
Impedance	115 Ohms (Unbalanced)
Capacitance	12.2Pf/ft
Inductance	14uH/ft
Propagation delay	1.4 ns/ft
Insulation resistance	1 G Ω /M min

5.2 Physical properties


ITEM		DESCRIPTION
UL Style		2651
Operating temperature		-20 °C - 105 °C
Flame test of cable		UL-VW-1
Conductor	Material	Tinned Copper Wire Stranded
	Construction	#28AWG, Stranded Tinner Cooper
Insulation	Material	Polyvinyl Chloride (PVC)



6. LEGAL INFORMATION

This document has been issued for informational purposes only. It can be updated or altered without any written notice. Riverdi cannot be held responsible for not announcing any changes or issuing next revisions or versions of this document.

Hi, I am here to help you!
If you have any additional
questions, please contact
our support via email:
contact@riverdi.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Riverdi:

[RVA-SWD-06M-C100](#)