




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. DIMENSIONS IN [] ARE METRIC.

RIBBON PART NUMBER	DESCRIPTION	ROLL 'B' WIDTH +/- 0.010 [0.254 mm]	QTY.
RMEH2BL	Ribbon, Hybrid, 2.50 inches wide, 300' long, for use with TDP43ME, Black	2.50 in [63.5 mm]	1
RMEH4BL	Ribbon, Hybrid, 4.25" wide, 300' long, for use with TDP43ME, Black	4.25 in. [108 mm]	1
RMER2BL	Ribbon, Resin, 2.50 inches wide, 300' long, for use with TDP4ME, Black	2.50 in [63.5 mm]	1
RMER2WH	Ribbon, Resin, 2.50" wide, 300' long, for use with TDP43ME, White	2.50 in [63.5 mm]	1
RMER4BL	Ribbon, Resin, 4.25" wide, 300' long, for use with TDP43ME, Black	4.25 in. [108 mm]	1
RMER4BL-A	Ribbon, Resin, 4.25" wide, 300' long, for use with TDP43ME, Black	4.25 in. [108 mm]	1
RMER4BL-C	Ribbon, Resin, 4.25" wide, 300' long, for use with TDP43ME, Black	4.25 in. [108 mm]	1
RMER4BU	Ribbon, Resin, 4.25" wide, 300' long, for use with TDP43ME, Blue	4.25 in. [108 mm]	1
RMER4RD	Ribbon, Resin, 4.25" wide, 300' long, for use with TDP43ME, Red	4.25 in. [108 mm]	1
RMER4WH	Ribbon, Resin, 4.33" wide, 300' long, for use with TDP43ME, White	4.33 in [110.0 mm]	1
RHEH4BL	Ribbon, Hybrid, 4.33" wide, for use with TDP4*HE Series Printer, Black	4.33 in [110.0 mm]	1
RHER4BL	Ribbon, Hybrid, 4" wide, for use with TDP4*HE Series Printer, Black, STANDARD	4.00 in [101.6 mm]	1
RHER4BL-A	Ribbon, Hybrid, 4" wide, for use with TDP4*HE Series Printer, Black, A-TYPE	4.00 in [101.6 mm]	1
RHER4BL-C	Ribbon, Hybrid, 4" wide, for use with TDP4*HE Series Printer, Black, C-TYPE	4.00 in [101.6 mm]	1
RHER4BL-E	Ribbon, Resin, 4" wide, for use with TDP4*HE Series Printer, Black, Ultra-durable, E-TYPE	4.00 in [101.6 mm]	1
RHER4WH	Ribbon, Resin, 4" wide, for use with TDP4*HE Series Printer, White	4.00 in [101.6 mm]	1
RMER1BL	Ribbon, Resin, 1.1" wide, 300' long, for use with TDP43ME, Black	1.10 in [27.9 mm]	1

PART NUMBER		SEE TABLE	
TITLE		THERMAL TRANSFER DESKTOP PRINTER INK RIBBONS	
ITEM REVISION NAME		CUSTOMER DRAWING	
M00313KG/11			
DATASET FILE NAME			
M00313KG_DC/11A C11739 CUST DWG			
		THIRD ANGLE PROJECTION	
MATERIAL		DRAWING NUMBER	
SEE TABLE		C11739	
DRAWN BY	DATE	CHK	SCALE
RVU	2/4/2021	MSAD	NONE
SHEET 1 OF 1			SIZE
			A

11A	10/11/2022	RVU	DAPE	MSAD	INITIAL RELEASE	GAECN05862
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

RMEH2BL