




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	19JAN2022	SCB	PS



2385004-3 AS SHOWN


77.00	20	2-2385004-0
73.19	19	1-2385004-9
69.38	18	1-2385004-8
65.57	17	1-2385004-7
61.76	16	1-2385004-6
57.95	15	1-2385004-5
54.14	14	1-2385004-4
50.33	13	1-2385004-3
46.52	12	1-2385004-2
42.71	11	1-2385004-1
38.90	10	1-2385004-0
35.09	9	2385004-9
31.28	8	2385004-8
27.47	7	2385004-7
23.66	6	2385004-6
19.85	5	2385004-5
16.04	4	2385004-4
12.23	3	2385004-3
8.42	2	2385004-2
DIM A	NO. OF POS.	TE PN


NOTES:

- 1 MATERIALS & FINISH
HOUSING : PA66, UL94 V0, COLOR - LIGHT GREEN
PUSH BUTTON : PA66, UL94 V0, COLOR - ORANGE
CONTACT : COPPER ALLOY, TIN PLATED
SPRING : STAINLESS STEEL
2. MECHANICAL
WIRE STRIPPING LENGTH : 9 - 10 mm
3. ELECTRICAL
WIRE RANGE : 16 - 28 AWG
RATED VOLTAGE : 300V
RATED CURRENT : 8A
INSULATION RESISTANCE : >2000 M Ohm (500V DC)

4. OPERATING TEMPERATURE RANGE : -40°C TO +105°C

5 TOLERANCE NOT CUMULATIVE



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11JAN2022 SHRIC HARANA B	 TE Connectivity		
		CHK 11JAN2022 SUBHASREE S			
		APVD 11JAN2022 PRASHANTH S			
		PRODUCT SPEC 108-32299			
DIMENSIONS: mm		APPLICATION SPEC 114-32242	NAME TERMINAL BLOCK, SPRING PLUG, PITCH 3.81mm		
		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-2385004
MATERIAL 1		FINISH 1	RESTRICTED TO -		
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2385004-5](#)