

APPLICATOR PARTS LIST				TYPE LENGTHWISE BUTTON CONTACT			AMP INCORPORATED HARRISBURG, PENNA.				
NO.	DESCRIPTION	REQ.	PART NO.	NO.	DESCRIPTION	REQ.	PART NO.	CRIMPING DATA			TERMINALS
1	WIRE CRIMPER 2.453920.6	1	470231	42				TO APPLY TERMINAL			40662-S
2	INS. CRIMPER			43							40792-S
3	ANVIL Wire	1	371028	44	Hold Down	1	375826	WIRE SIZE	CRIMP HEIGHT		40911-S
4	ANVIL SPACER			45				16	.068		42523-S
5	SHEAR BLADE	1	387142	46				18	.064		
6	REAR SHEAR PLATE 395012-0	1	371311	47				20	.060		
7	SHEAR BLADE SPACER	2	371027	48				CRIMP	SIZE	TYPE	FEED
8	FRONT SHEAR PLATE			49				WIRE	.120	F	.234
9	REAR ANVIL SPACER PLT.	1	385788	50				INSUL.			
10	FRONT ANVIL SPACER PLT.			51				SLEEVED			
11	TOOL SPACER	1	370827	52				INSULATION RANGE		WIRE RANGE	
12	CRIMP SPACER			53						20 - 16	
13	FRONT STRIP GUIDE	1	371638	54				EXPLODED VIEW			
14	REAR STRIP GUIDE	1	371638	55				A-6000 A-6000-1			
15	RAM	1	471911	56				REMARKS: TAB SHEARED DOWN			
16	TOOL HOLDER			57							
17	ADJ. CRIMP MOUNT			58							
18	ADJ. BLOCK			59							
19	APPLICATOR MOUNT ASSY.	1	570656	60							
20	BASE PLATE			61							
21	BASE BLOCK			62							
22	STRIP GUIDE PLATE			63							
23	ANVIL HOLDER	1	385684	64							
24	AUX. ANVIL HOLDER	1	377515	65	TENSION ROLL PLATE	1	374999				
25	STRIPPER	1	371183	-MISCELLANEOUS-							
26	STRIPPER MOUNT	1	370660	66	LUBRICATOR ASSY.	1	465184-2				
27	RETAINER PLATE	1	372251	67	SYNTHETIC OIL	1	22014-1				
28	STRIPPER MOUNT BRACKET	2	371628	68							
29	STRIPPER BUSHING			69							
30	STOCK DRAG	1	375381	70							
31	STOCK DRAG HANDLE	1	375382	71							
32	STOCK DRAG STUD	2	334045-1	72	MEAL FEED ASSY	1	692140-2				
33	STOCK DRAG SPRING 1-23847-1	2	370795	REV.	REVISION RECORD	DATE	BY	ECN			
34	STOCK DRAG ADJ. SCREW	2	372997	K	0150-6407-95	9/85	LAC	OE			
35	FEED FINGER HOLDER										
36	FEED FINGER	1	379571								
37	FEED FINGER TIP										
38	FEED FINGER SPACER										
39	BASE CASTING	1	570238								
40	GUARD Front 457664-2	1	470262								
41											

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INC. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

■ DENOTES WEARING PARTS
RECOMMEND PURCHASE REPLACEMENT

THIS APPLICATOR IS TO BE USED ON
AMP-O-LECTRIC 1-471273-3
AMP-O-MATIC 1-471273-3

SERIAL NO. _____ DATE SHIPPED _____

CUSTOMER NAME AND ADDRESS _____

APPLICATOR NUMBER _____ REV. **K** 670181-2

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[670181-2](#)