

IE-S-IP67**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Junction box, design for SnapIn plug-in connectors ver.6
according to IEC 61076-3-106, plastic

General ordering data

Version	Connecting plug, Junction box, IP67, Cat.6A / Class E _A (ISO/IEC 11801 2010), Variant 6 to IEC 61076-3-106
Order No.	8808370000
Type	IE-S-IP67
GTIN (EAN)	4032248505951
Qty.	1 pc(s).

Creation date September 18, 2022 3:43:09 AM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

IE-S-IP67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	90 g
------------	------

Temperatures

Operating temperature	-40 °C...70 °C
-----------------------	----------------

General data

Colour	Configuration	Screw-on junction box including RJ45 module with IDC connection
Light Grey		
Protection degree	Type of mounting	Floor-mounted, for exposed connections, Wall mounting
IP67		
Wiring	EIA/TIA T568 A, EIA/TIA T568 B	

General standards

Certificate No. (DNVGL)	TAE00003EW	Connector standard	IEC 61076-3-106 Var. 6
-------------------------	------------	--------------------	------------------------

Technical data RJ45 module

Wiring	EIA/TIA T568 A, EIA/TIA T568 B
--------	--------------------------------

Technical specifications for power connector

Number of poles	8
-----------------	---

Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ECLASS 9.0	27-44-03-90
ECLASS 9.1	27-44-03-90	ECLASS 10.0	27-44-03-90
ECLASS 11.0	27-44-03-90	ECLASS 12.0	27-44-03-90

Approvals

Approvals



ROHS	Conform
------	---------

IE-S-IP67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of
Conformity

[GOST Approval](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[MAN IE GUIDE DE](#)

[MAN IE GUIDE EN](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)

[PI PROFINET CABLING EN](#)

[PI PROFINET CABLING EN](#)

IE-S-IP67

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[8808370000](#)