


TS 35X15/6X25 2M/ST/ZN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Version	Rail, TS 35, TS 35 x 15, with slot, Steel, galvanic zinc plated and passivated
Order No.	1866290000
Type	TS 35X15/6X25 2M/ST/ZN
GTIN (EAN)	4032248435388
Qty.	2 m

TS 35X15/6X25 2M/ST/ZN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	15 mm	Depth (inches)	0.591 inch
Height	35 mm	Height (inches)	1.378 inch
Width	2,000 mm	Width (inches)	78.74 inch
Net weight	620 g		

Mounting rail

Installation advice	Direct mounting	
Length of the terminal rail	nominal	2,000 mm
	min.	0 mm
	max.	2,000 mm
Material	Steel	
Mounting rail not punchable	Yes	
Pre-punched mounting rail	Yes	
Short circuit strength corresponds to E-Cu wire	50 mm ²	
Short-time withstand current according to IEC 60947-7-2	6 kA/1s	
Slit gap	11 mm	
Slit gap		
Slit length	25 mm	
Slit length		
Slit width	6.3 mm	
Slit width		
Slotted drill holes	Yes	
Spacing of holes, centre-to-centre	36 mm	
Standards	In accordance with DIN EN 60715	
Surface finish	galvanic zinc plated and passivated	

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ECLASS 9.0	27-40-06-02
ECLASS 9.1	27-40-06-02	ECLASS 10.0	27-40-06-02
ECLASS 11.0	27-40-06-02	ECLASS 12.0	27-40-06-02

Approvals

ROHS	Conform
------	---------

Downloads


Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD, Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

TS 35X15/6X25 2M/ST/ZN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1866290000](#)