

RED INDICATES ORIGINAL


DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS, INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR REPRODUCTION OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.

REVIEWS			310-0062		SH 1
REV	EO	DESCRIPTION	OWN	APPROVED	DATE
L	12388	ADDED -224 & -225 NOTE 3 THREADED WAS 4 LUG; SEE ECO	DBN	WM	4-8-98

DASH NO	CABLES ACCOMMODATED	A DIM	B DIA	C HEX	ASSEMBLE PER
-201	M17/178-00002	1.146	.339	.255	TAI-143
-202	TWC-78-1				
-203	TWC-124-1A				
-204	10602, RAYCHEM				
-205	TWAC-78-1F2				
-206	782600130, RAYCHEM	1.352	.442	.344	TAI-167
-207	83310 BELDEN				
-208	202-3927 MICRODOT	1.146	.339	.255	TAI-143
-209	202-3942 MICRODOT				
-210	8451 BELDEN	1.352	.442	.344	TAI-144
-211	202-3934 MICRODOT				
-212	2524E0114, RAYCHEM				
-213	TWC-78-2				
-214	TWC-124-2				
-215	BL-982 TIMES	1.146	.339	.255	TAI-143
-216	BL-1242 TIMES				
-217	GC875TM24H, GRUMMAN				
-218	EPO 221888, RAYCHEM				
-219	252601114, RAYCHEM				
-220	GC875RR1, GRUMMAN	1.352	.442	.344	TAI-144
-221	10614, RAYCHEM				
-222	10613, RAYCHEM				
-223	HMS2-1148, HUGHES				
-224	TWCP-124-3				
-225	PS685PL, PRIME STOCK				

DASH NO	CABLES ACCOMMODATED	A DIM	B DIA	C HEX	ASSEMBLE PER
-301	GC875GC1, GRUMMAN	1.146	.339	.255	TAI-153
-302	GC875GB1, GRUMMAN				
-303	5022E5111, RAYCHEM				
-304	7528A5314, RAYCHEM	1.352	.442	.344	TAI-173
-305	M17/177-00001				
-306	295-3804 MICRODOT				
-307	TRC-50-2	1.146	.339	.255	TAI-153
-308	M17/134-00002				
-309	TRC-75-1				
-310	TRC-75-2	1.352	.442	.344	TAI-198
-311	TRC-50-1				

INCH	MM
.005	0.13
.030	0.76
.255	6.48
.339	8.61
.344	8.74
.442	11.23
.455	11.56
1.00	25.40
1.146	29.11
1.25	31.75
1.352	34.34
1.75	44.45



-207 SHOWN

1. SHRINKABLE STRAIN RELIEF AND/OR SHRINKABLE SEALING SLEEVE SUPPLIED LOOSE AS FOLLOWS:
- CABLE GROUPS -207, -210 & -307:
 - 1 SHRINKABLE STRAIN RELIEF (1.00 LONG)
 - 1 SHRINKABLE SEALING SLEEVE (1.25 LONG)
 - CABLE GROUPS -201 THROUGH -206, -208, -209, -217 THROUGH -223, -301, -302, -303 & -309:
 - 1 SHRINKABLE SEALING SLEEVE (1.25 LONG)
 - CABLE GROUPS -211 THROUGH -216, -305, -306 & -308:
 - 1 SHRINKABLE STRAIN RELIEF (1.75 LONG)
3. THREADED SUBMINIATURE CONCENTRIC TWINAX (4 PIECE ASSY) AND TRIAX (6 PIECE ASSY), FULL CRIMP CABLE PLUG
2. FINISH: TFS-1A (NICKEL)
1. ALL DIM ARE IN INCHES

6. EXAMPLE OF COMPLETE MODEL NO:
PL3155AC-201
- BASIC MODEL NO. CABLE GROUP DASH NO
5. EXAMPLE OF COMPLETE PART NO:
310-0062-201
- BASIC PART NO. CABLE GROUP DASH NO



RECOMMENDED
HEX CRIMP
SCALE: NONE

QTY	DESCRIPTION		PART NUMBER	ITEM
TOL UNLESS SPECIFIED	.XX ± .03 .XXX ± .005 .XXXX ± .0002 ANGLES		PL3155AC/PL3155ACS	
DWN	DBN	4/6/98	MATERIAL	CODE IDENT
CHK	WM	4-7-98	14949	DRAWING NO.
ENGR				REV
APPR				L
NEXT ASSY	APPR	4-8-98	SCALE 4/1	DATE 7-2-85
				SHEET 1 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[PL3155ACS-201](#)