

Portable Charger for Apple Watch - Lightning, Magnetic and USB-A Output, 5200mAh Power Bank, Lithium-Ion, MFi

MODEL NUMBER: UPB-05K2-APL



Portable power bank charges your Apple Watch and 2 smartphones, tablets or other mobile devices.

Features

5200mAh Lithium-Ion Battery Charges Your Apple Watch without an AC Power Outlet

No more frantic searching for an outlet when your mobile device's battery power is getting low. Small and lightweight, this high-capacity power bank dishes out 5200mAh of battery capacity for charging up to three mobile devices, including smartphones, tablets, e-readers, handheld gaming devices and an Apple Watch. Lithium-ion lasts longer than lead-acid batteries and saves you money in the end. The UPB-05K2-APL is compatible with Apple, Android and Windows devices.

Magnetic Module Keeps Your Apple Watch Charged and Ready to Use

Place your Apple Watch on the magnetic module for safe, efficient wireless charging while you're at the office, resting after a hike or relaxing at the hotel after sightseeing.

Built-In Lightning Cable and USB Port Keeps Other Essential Devices Charged Too

The Lightning cable provides 5V 2.4A (12W) of charging power for your iPhone, iPad or other charging device. It folds neatly into the bottom of the power bank to protect it from damage and cut down on cable clutter when not in use. A USB-A port also provides 12W of total power for Android, Windows and other mobile devices (cable sold separately).

Protects Your Expensive Devices During Charging

Comprehensive safety features ensure worry-free charging of mobile devices. The UPB-05K2-APL protects your devices against short circuit, over-voltage, over-current, over-charge and over-discharge. Total output current cannot exceed 5V 2.4A (12W). Otherwise, the over-current protection will activate and charging will be halted.

Easy to Recharge for the Next Time You Leave Home

A lithium-ion battery with 5200mAh of capacity provides charging at maximum power draw for hours, making your devices ready when you need them. Status LEDs let you know how much battery capacity is left. When it's time to charge the internal battery, connect a Lightning cable (sold separately) to connect the power bank's Lightning port to a computer or wall charger.

Compact Housing Packs in a Pocket for On-the-Go Charging

An ideal power solution when you're on the road or stuck somewhere without convenient electricity, the portable all-in-one battery charger weighs less than one pound. It fits comfortably in your purse, pocket or backpack to keep your Apple Watch, smartphone, tablet or other handheld device operating when you

Highlights

- Ideal for road trips, hikes, blackouts and other applications without AC power
- Magnetic charging module provides quick power boost for your Apple Watch
- Built-in Lightning cable delivers 5V 2.4A (12W) for charging Apple devices
- USB-A port offers 12W maximum charging power for tablets and smartphones
- 5200mAh of lithium-ion battery capacity is plenty for hours of maximum power draw

System Requirements

MFi-certified for use with the latest generation of Apple Watch, iPhone, iPad and iPod devices

Package Includes

- UPB-05K2-APL 5200mAh Portable Charger for Apple Watch
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

need it. And it's good looking too!

Specifications

OVERVIEW	
UPC Code	037332264039
Product Type	Portable Charger
Charging Form Factor	Portable
Device Compatibility	Amazon Kindle; Phone; Tablet; Watch
Technology	USB
Country/Region	Global
INPUT	
Nominal Input Voltage(s) Supported	5V DC
Input Plug Type	Lightning (FEMALE)
Input Plug Type Details	User Supplied Lightning Cable
OUTPUT	
Output Capacity (Watts)	12
Continuous Output Capacity (Watts)	12
Overload Protection	Yes
BATTERY	
Capacity (Ah)	5.2
POWER	
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Number of Ports	3
Side A - Connector 1	LIGHTNING (FEMALE)
Side B - Connector 1	Magnetic Charger
Side B - Connector 2	USB A (FEMALE)
Side B - Connector 3	LIGHTNING (MALE)
VOLTAGE REGULATION	
Overvoltage Correction	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	LED's will illuminate to indicate USB Device Charging Status as well as Power Bank Charging Status. See manual for LED information.
CHARGING	
Number of Charging Ports	3
Total Charging Amps	2.4A
Total Charging Watts	12
Charging Method	Magnetic Charger; USB; Wireless
Charging Method Detail	5,200 mAh
Charging Port Type	LIGHTNING (MALE); Magnetic Charger; USB A (FEMALE)
Charging Ports Details	Lightning and USB-A: 5V/2.4A, 12W
Charging Ports / Amps	2.4A
Magnetic Charging	Yes
Wireless Charging	Yes
Overcharge Protection	Yes
Compatible Devices	Smartphone
Boost Converter Efficiency	90%
PHYSICAL	
Color	Silver; White
Material of Construction	ABS/PVC
Total Number of Ports	2
Unit Dimensions (hwd / in.)	2.760 x 1.220 x 3.070
Unit Dimensions (hwd / mm)	168 x 76 x 18
Unit Packaging Type	Box
Unit Weight (lbs.)	0.61
Unit Weight (kg)	0.28
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C) - Charge; 14° to 122°F (-10° to 50°C) Discharge; 41° to 77°F (5° to 25°C)
Storage Temperature Range	14° to 113°F (-10° to 45°C)
Operating Humidity Range	45% to 75% RH, Non-Condensing
Storage Humidity Range	20% to 75% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
GaN Technology	No



Powering Business Worldwide

TRIPP LITE
SERIES

Overcurrent Protection	Yes
Overvoltage Protection	Yes
Over Current Protection	Yes
Quick Charge Compliant	No
Driver Required	No
STANDARDS & COMPLIANCE	
Product Certifications	MFi
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[UPB-05K2-APL](#)