


24 AWG (0.020"  $\pm$  0.002" DIAMETER),  
TINNED CCS, 1.00" LONG MINIMUM



RESISTANCE @ +25°C = 2,000,000  $\Omega$   $\pm$  10%  
 RESISTANCE TEMPERATURE CURVE = "V4"  
 TEMPERATURE COEFFICIENT @ +25°C = -4.85%/°C NOMINAL  
 BETA " $\beta$ " (0 TO +50°C) = 4,288°K NOMINAL  
 DISSIPATION CONSTANT = 2 mW/°C NOMINAL (STILL AIR)  
 THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (STILL AIR)  
 THERMAL TIME CONSTANT = 0.5 SECONDS NOMINAL (STIRRED OIL)  
 MAXIMUM TEMPERATURE RATING = +300°C

---	ISO RELEASE	02/22/05	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP. 1832 W. COLLINS AVE. ORANGE, CA 92867 714-639-1000 www.ussensor.com	
DRAWN BY	DAN DANKERT		
DATE	05/15/98	NTC THERMISTOR	
REV	NONE	P/N 205V4G1K	
LAYER	0 OF 1		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[205V4G1K](#)