


# MI1206K260R-10


**UNCONTROLLED  
DOCUMENT**

## PHYSICAL DIMENSIONS:

A	3.20 [.126]	+ 0.20 [.008]
B	1.60 [.063]	+ 0.20 [.008]
C	1.10 [.043]	+ 0.20 [.008]
D	0.51 [.020]	+ 0.25 [.010]




Z vs FREQUENCY  
IMPEDANCE UNDER DC BIAS



FREQUENCY (MHz)

|Z|, R, AND X vs. FREQUENCY




FREQUENCY (MHz)

Z R X<sub>L</sub>

AGILENT E4991A RF Impedance/Material Analyzer  
HP 16194A Test Fixture. TEST REF. 3298

## LAND PATTERNS FOR REFLOW SOLDERING



(For wave soldering, add 0.762  
(.030) to this dimension)


## ELECTRICAL CHARACTERISTICS:

Z @ 100MHz ( Ω )	DCR ( Ω )	Rated Current
Nominal	26	
Minimum	20	
Maximum	33	0.060 1500 mA

NOTES: UNLESS OTHERWISE SPECIFIED

1. TAPED AND REELED per CURRENT EIA SPECIFICATIONS 7" REELS, 3000 PCS/REEL.
2. COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.
3. TERMINATION FINISH IS 100% TIN.
4. OPERATING TEMP. RANGE: -40°C~+125°C. (INCLUDING SELF-HEATING)

## RECOMMENDED SOLDERING CONDITIONS



DIMENSIONS ARE IN mm [INCHES]				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
C	ADD OPERATING TEMPERATURE UPDATE LAIRD LOGO AND REFLOW CURVE	08/05/13	QU	PROJECT/PART NUMBER: <b>MI1206K260R-10</b>			
B	UPDATE COMPANY LOGO ADD ROHS	8/20/08	JRK				
A	ORIGINAL DRAFT	04/13/04	JRK	DATE:	04/13/04	SCALE:	NTS
REV	DESCRIPTION	DATE	INT	CAD #	MI1206K260R-10-C	TOOL #	-
				REV		PART TYPE:	CO-FIRE
						DRAWN BY:	JRK
						SHEET:	2 of 2

**Laird**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Laird:

[MI1206K260R-10](#)