



RESISTANCE @ +25°C = 20,000  $\Omega$  NOMINAL  
 ACCURACY (0 TO +70°C) =  $\pm 0.20^\circ\text{C}$   
 RESISTANCE/TEMPERATURE CURVE = "J"  
 TEMPERATURE COEFFICIENT @ +25°C =  $-4.4\%/^\circ\text{C}$  NOMINAL  
 BETA " $\beta$ " (0 TO +50°C) = 3,892°K NOMINAL  
 DISSIPATION CONSTANT = 1 mW/°C NOMINAL  
 THERMAL TIME CONSTANT = 10 SECONDS MAXIMUM (STILL AIR)  
 THERMAL TIME CONSTANT = 1 SECOND MAXIMUM (WELL STIRRED OIL)  
 MAXIMUM TEMPERATURE RATING = +150°C

MAXIMUM STORAGE AND OPERATION TEMPERATURE FOR BEST LONG-TERM STABILITY = +120°C

REV	REVISION RECORD	DATE	APP
---	ISO RELEASE	06/12/03	DD

SCALE NONE	© COPYRIGHT <b>U.S. SENSOR CORP.</b> 714-639-1000 <a href="http://www.ussensor.com">www.ussensor.com</a> <b>NTC THERMISTOR</b> P/N PT203J2
DRAWN BY DAN DANKERT	
DATE 08/19/96	
REV. NONE	
LAYER 0 OF 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[PT203J2](#)