


New
BK250A
A size (HR17/50)

Low temperature discharge type



Dimensions (with tube)



Specifications


Diameter		17.0 +0.0 / -0.7 mm	
Height		50.0 +0.0 / -2.0 mm	
Approximate Weight		40 g	
Nominal Voltage		1.2 V	
Discharge Capacity ^{*1}	Average ^{*2}	2600 mAh	
	Rated (min.)	2450 mAh	
Approx. Internal impedance at 1000Hz at charged state.		20 mΩ	
Charge	Standard	245 mA X 16 hrs.	
	Rapid ^{*3}	2450 mA X 1.2 hrs.	
Ambient Temperature	Charge	Standard	-10 °C to 45 °C
		Rapid	0 °C to 40 °C
	Discharge		-30 °C to 65 °C
	Storage	<1 year	-30 °C to 35 °C
		<6 months	-30 °C to 45 °C
		<1 month	-30 °C to 55 °C

*1 After charging at 0.1 It for 16 hours, discharging at 0.2 It.


*2 For reference only.

*3 Need specially designed control system. Please contact Panasonic for details.

Typical charge characteristics



Typical discharge characteristics



Battery performance and cycle life are strongly affected by how they are used. In order to maximize battery safety, please consult Panasonic when determining charge/discharge specs, warning label contents and unit design.

*The data in this document are for descriptive purposes only and are not intended to make or imply any guarantee or warranty.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

[BK-250AB01](#) [BK-26SCSA01](#)