

# Input module - UM- D25SUB/F/PTS/MSTB/1855-AI - 2319773

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Analog VARIOFACE input module, with COMBICON screw connection and a 25-pos. D-SUB female connector. The signal path can be interrupted with a disconnect knife.



## Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 427739
GTIN	4046356427739
Custom tariff number	85369010
Note	Made to Order (non-returnable)

## Technical data

### Dimensions

Width	91.5 mm
Height	111 mm
Depth	56 mm

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

### General

Max. perm. operating voltage	50 V AC/DC
Max. perm. current (per branch)	2 A
Status display	No
Mounting position	any

### Connection data for connection 1

Connection name	Field level
Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross section solid	0.2 mm² ... 2.5 mm²
Conductor cross section flexible	0.2 mm² ... 2.5 mm²
Conductor cross section AWG	24 ... 12

### Connection data for connection 2

Connection name	Controller level
-----------------	------------------

## Input module - UM- D25SUB/F/PTS/MSTB/1855-AI - 2319773

### Technical data

#### Connection data for connection 2

Connection method	D-SUB socket strip
Number of positions	25

#### Standards and Regulations

Designation	Air clearances and creepage distances
Standards/regulations	DIN EN 50178
Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (basic insulation)
Degree of pollution	2
Overvoltage category	II

#### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2319773