XY2CE1A270H7

e-stop rope pull switch XY2CE - RH side -2NC - booted pushbutton

Product availability: Non-Stock - Not normally stocked in distribution facility



Main Commercial Status Commercialised Range of product Preventa XY2 Product or component Latching emergency stop rope pull switch type Device short name XY2CE Local signalling Without pilot light Number of cables Trigger cable maximum 229.66 ft (70 m) length Red RAL 3000 Housing colour Reset By booted pushbutton Contacts type and 2 NC composition Trigger cable anchor RH side

Screw clamp terminal 1 x 0.5...2 x 1.5 mm²

Complementary

Contacts operation	Slow-break
Tightening torque	7.0810.62 lbf.in (0.81.2 N.m)
Cable entry number	3 plain hole for 1/2" NPT conduit entry
Mechanical durability	10000 cycles
Distance between cable supports	16.4 ft (5 m)
[le] rated operational current	0.27 A at 250 V DC-13, Q300 conforming to EN/IEC 60947-5-1 appendix A 3 A at 240 V AC-15, A300 conforming to EN/IEC 60947-5-1 appendix A
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	300 V conforming to CSA C22.2 No 14 400 V, degree of pollution: 3 conforming to EN/IEC 60947-1 300 V conforming to UL 508
[Uimp] rated impulse withstand voltage	6 kV
Positive opening	With conforming to EN/IEC 60947-5-1
Resistance across terminals	<= 25 MOhm conforming to NF C 93-050 method A <= 25 MOhm conforming to EN/IEC 60255-7 category 3
Short circuit protection	10 A cartridge fuse, gG conforming to EN/IEC 60269
Height	5.59 in (142 mm)
Width	9.02 in (229 mm)
Depth	4.13 in (105 mm)
Terminals description ISO n°1	(21-22)NC (11-22)NC
Product weight	3.2 lb(US) (1.45 kg)

point

Connections - terminals

Environment

Standards	EN/IEC 60947-5-1
	EN/IEC 60947-5-5
	EN/ISO 13850
	UL 508
	Machinery directive 2006/42/EC
	Work equipment directive 2009/104/EC
Safety level	Can reach SIL 3 conforming to EN/IEC 61508
	Can reach category 4 conforming to EN/ISO 13849-1 (with the appropriate
	monitoring system and correctly wired)
	Can reach PL = e conforming to EN/ISO 13849-1 (with the appropriate
	monitoring system and correctly wired)
Safety reliability data	B10d = 50000 (value given for a life time of 20 years limited by mechanical or
	contact wear)
Product certifications	CCC
	CSA
	UL
Protective treatment	TC
Ambient air temperature for operation	-13158 °F (-2570 °C)
Ambient air temperature for storage	-40158 °F (-4070 °C)
Vibration resistance	10 gn (f = 10300 Hz) conforming to EN/IEC 60068-2-6
Shock resistance	50 gn (11 ms) conforming to EN/IEC 60068-2-27
IP degree of protection	IP65

Ordering and shipping details

Category	22441 - LIMIT SWITCHES,CABLE PULL
Discount Schedule	Т
GTIN	00785901945550
Nbr. of units in pkg.	1
Package weight(Lbs)	3.55
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	N
Country of origin	MA

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0852 - Schneider Electric declaration of conformity
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Period	18 months



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schneider Electric: XY2CE1A270H7