

L1442M

L140 cable pull limit switch - 2 contacts - maintained - CCW - 1/2" NPT

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Commercial Status	Commercialised
Range of product	L140
Series name	Severe duty mill
Product or component type	Limit switch
Product specific application	Cable pull switch
Device short name	L140
Body type	Fixed
Head type	Rotary head
Sale per indivisible quantity	1

Complementary

Base plate style	Style 2
Body material	Cast aluminum
Fixing mode	By the body
Type of operator	Spring return without operating lever
Function available	-
Switch actuation	CCW From right
Type of approach	Vertical approach
Electrical connection	Screw-clamp terminals (AWG: 22...12)
Cable entry	1 entry for 1/2" - 14 NPT conforming to ANSI B1.20.1
Number of poles	2
Contacts type and composition	1 NC + 1 NO
Contacts style	A
Switch function	DPDT-DB
Contact form	Form Zb
Contacts material	Silver on steel backing moveable contact 90/10 AgCdO on copper backing stationary contact
Contacts usage	-
Contacts operation	Snap action
Positive opening	Without
Minimum torque for tripping	208 ozf.in
Minimum torque for resetting	112 ozf.in
Tripping angle	17 ° - for cable operated stop switch
Maximum displacement angle	80 °
Repeat accuracy	+/- 0.03 %
Contact code designation	P600 , DC (Ue = 120 V, Ie = 5 A) conforming to NEMA rating designation P600 , DC (Ue = 250 V, Ie = 1 A) conforming to NEMA rating designation P600 , DC (Ue = 600 V, Ie = 0.2 A) conforming to NEMA rating designation A600 , AC (Ue = 120 V, Ie = 20 A) conforming to NEMA rating designation A600 , AC (Ue = 240 V, Ie = 12.5 A) conforming to NEMA rating designation A600 , AC (Ue = 480 V, Ie = 6.25 A) conforming to NEMA rating designation A600 , AC (Ue = 600 V, Ie = 5 A) conforming to NEMA rating designation
[Ithe] conventional enclosed thermal current	20 A
[Ui] rated insulation voltage	600 V (degree of pollution: 3) conforming to CSA C22.2 No 14 600 V (degree of pollution: 3) conforming to UL 508 600 V (degree of pollution: 3) conforming to IEC 60947-1

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

[Uimp] rated impulse withstand voltage	2.64 kV AC for 1 minute conforming to CSA 2.2 kV AC for 1 minute conforming to UL 2.5 kV AC for 1 minute conforming to CE
Short circuit protection	20 A Bussmann class CC KTK-R-20 fuse with non-time delay
Width	2.25 in
Height	4.95 in
Depth	3.41 in
Product weight	1.5 lb(US)

Environment

Shock resistance	30 gn for 9 ms conforming to IEC 60068-2-27
Vibration resistance	10 gn (f = 10...55 Hz) conforming to IEC 60068-2-6
NEMA degree of protection	NEMA 13 conforming to Nema type 250 NEMA 12 conforming to Nema type 250 NEMA 4 conforming to Nema type 250 NEMA 2 conforming to Nema type 250 NEMA 1 conforming to Nema type 250
IP degree of protection	IP67 conforming to IEC 60529
Class of protection against electric shock	Class 0 conforming to IEC 61140
Ambient air temperature for operation	-20...120 °F
Ambient air temperature for storage	-20...120 °F
Protective treatment	Corrosion resistant gray paint

Ordering and shipping details

Category	22426 - LIMIT SWITCHES,TYPE L
Discount Schedule	T
GTIN	00785901169796
Nbr. of units in pkg.	1
Package weight(Lbs)	1.50
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	N
Country of origin	MX

Contractual warranty

Period	18 months
--------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[L1442M](#)