TeSys GV2-Circuit breaker-thermal-magnetic - 13...18 A - screw clamp terminals



Product availability: Stock - Normally stocked in distribution facility



Main Commercial Status Commercialised Range of product TeSys GV2 **GV2ME** Device short name Circuit breaker Product or component type Circuit breaker Motor protection application Poles description 3P AC Network type Utilisation category Category A conforming to IEC 60947-2 AC-3 conforming to IEC 60947-4-1 Network frequency 50/60 Hz conforming to IEC 60947-4-1 Breaking capacity Icu = 100 kA at 230/240 V AC 50/60 Hz conforming to IFC 60947-2 Icu = 6 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 Icu = 8 kA at 440 V AC 50/60 Hz conforming to IEC Icu = 15 kA at 400/415 V AC 50/60 Hz conforming to IEC 60947-2 Icu = 3 kA at 690 V AC 50/60 Hz conforming to IEC 60947-2 [lcs] rated service 50 % at 440 V AC 50/60 Hz conforming to IEC short-circuit breaking 60947-2 capacity 75 % at 690 V AC 50/60 Hz conforming to IEC 60947-2 100 % at 230/240 V AC 50/60 Hz conforming to IEC 60947-2 50 % at 400/415 V AC 50/60 Hz conforming to IEC 60947-2 75 % at 500 V AC 50/60 Hz conforming to IEC 60947-2 13...18 A Thermal protection adjustment range Trip unit technology Thermal-magnetic Magnetic tripping 223 A

Complementary

Mounting mode	By clips	
	By screws	
Mounting support	Rail	
Mounting position	Horizontal	
	Vertical	
Motor power kW	15 kW at 690 V AC 50/60 Hz	
	9 kW at 500 V AC 50/60 Hz	
	7.5 kW at 400/415 V AC 50/60 Hz	
Control type	Pushbutton	
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-2	
[Ui] rated insulation voltage	690 V AC 50/60 Hz conforming to IEC 60947-2	
[Ith] conventional free air thermal current	18 A conforming to IEC 60947-4-1	
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-2	
Power dissipation per pole	2.5 W	

r technical characteristics of the performance of the products contained herein. mining suitability or reliability of these products for specific user applications. risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof the responsible or itable for misuse of the information contained herein. or and is not to be united and its appropriate are its affiliates or subs information provided in this documentation conta s documentation is not intended as a substitute for the cluby of any such user or integrator to perform ther Schneider Electric Industries SAS nor any of The information

current

Mechanical durability	100000 cycles
Electrical durability	100000 cycles for AC-3 at 440 V
Operating rate	25 cyc/h
Rated duty	Continuous conforming to IEC 60947-4-1
Connections - terminals	Screw clamp terminals 2 cable(s) 00.01 in² (14 mm²) - cable stiffness : flexible - with cable end Screw clamp terminals 2 cable(s) 00.01 in² (1.56 mm²) - cable stiffness : flexible - without cable end Screw clamp terminals 2 cable(s) 00.01 in² (16 mm²) - cable stiffness : solid
Tightening torque	15.04 lbf.in (1.7 N.m) - on screw clamp terminals
Mechanical robustness	Shocks 30 Gn for 11 ms conforming to IEC 60068-2-27 Vibrations 5 Gn, 5150 Hz conforming to IEC 60068-2-6
Suitability for isolation	Yes conforming to IEC 60947-1
Phase failure sensitivity	Yes conforming to IEC 60947-4-1
Height	3.5 in (89 mm)
Width	1.77 in (45 mm)
Depth	3.08 in (78.2 mm)
Product weight	0.57 lb(US) (0.26 kg)

Environment

Liviloriment	
Standards	EN 60204 IEC 60947-1 IEC 60947-2 IEC 60947-4-1 NF C 63-120 NF C 63-650 NF C 79-130 UL 508 VDE 0113 VDE 0660 CSA C22.2
Product certifications	ATEX BV CCC CEBEC CSA DNV EZU GL GOST RINA SETI TSE UL LROS
Protective treatment	TH
IP degree of protection	IP20 conforming to IEC 60529
IK degree of protection	IK04
Ambient air temperature for operation	-4140 °F (-2060 °C)
Ambient air temperature for storage	-40176 °F (-4080 °C)
Fire resistance	1760 °F (960 °C) conforming to IEC 60695-2-1
Operating altitude	6561.68 ft (2000 m)

Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	l11
GTIN	00785901211990
Nbr. of units in pkg.	1
Package weight(Lbs)	0.64
Product availability	Stock - Normally stocked in distribution facility
Returnability	Υ
Country of origin	FR



Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0631 - Schneider Electric declaration of conformity
REACh	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Period	18 months	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schneider Electric:

GV2ME20