XUK2LAPSMM12R

photo-electric laser sensor - XUK - thru beam receiver - Sn 30m - 10..30VDC -M12

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Commercial Status	Commercialised
Range of product	OsiSense XU
Series name	Application assembly Application food and beverage single mode
Electronic sensor type	Photo-electric sensor
Sensor name	XUK
Sensor design	Compact 50 x 50
Detection system	Thru beam
Material	Plastic
Type of output signal	Discrete
Supply circuit type	DC
Wiring technique	4-wire
Discrete output type	PNP
Discrete output function	1 NO or 1 NC programmable
Electrical connection	1 male connector M12, 4 pins
Product specific application	-
[Sn] nominal sensing distance	82.02 ft (25 m) thru beam need transmitter XUK2LAKSMM12T
· · · · · · · · · · · · · · · · · · ·	

Complementary

Complementary	
Enclosure material	ABS/PC
Lens material	PMMA
Maximum sensing distance	98.43 ft (30 m) thru beam
Output type	Solid state
Status LED	1 LED (green) for supply 1 LED (yellow) for output state
[Us] rated supply voltage	1030 V DC with reverse polarity protection
Supply voltage limits	933 V DC
Switching capacity in mA	<= 100 mA (overload and short-circuit protection)
Switching frequency	<= 3500 Hz
Voltage drop	<= 2.4 V (closed state)
Current consumption	<= 30 mA (no-load)
Delay first up	< 60 ms
Delay response	< 25 ms
Delay recovery	< 25 ms
Setting-up	Sensitivity adjustment by teach mode
Depth	1.97 in (50 mm)
Height	1.97 in (50 mm)
Width	0.71 in (18 mm)
Product weight	0.08 lb(US) (0.035 kg)

Environment

Product certifications	CE Ecolab
Ambient air temperature for operation	-4140 °F (-2060 °C)
Ambient air temperature for storage	-4176 °F (-2080 °C)
Vibration resistance	7 gn, amplitude = +/- 1.5 mm (f = 1055 Hz) conforming to IEC 60068-2-6
Shock resistance	30 gn (duration = 11 ms) conforming to IEC 60068-2-27
IP degree of protection	IP69K conforming to DIN 40050 IP67 conforming to IEC 60529

Ordering and shipping details

22481 - SENSORS, PHOTOELECTRIC
DS2
003389119077552
1
0.08
Non-Stock - Not normally stocked in distribution facility
N
DE

Contractual warranty

Period	18 months
--------	-----------



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schneider Electric: XUK2LAPSMM12R