







SPEED (SECONDS)	MODEL NUMBER
5	5M5011CT
15	15M5011CT
30	30M5011CT
60	60M5011CT

SPECIFICATIONS												
INPUT				OUTPUT		SHAFT ROTATION TO INCREASE VOLTAGE	TERMINAL CONNECTIONS					
WIRING	VOLTS	HERTZ	VOLTS	CONSTANT CURRENT LOAD			FOR INCREASING VOLTAGE AS VIEWED FROM ROTOR END					
				MAX. AMPS	MAX. KVA							
						INPUT		OUTPUT				
SINGLE PHASE	120	50/60	0-140	50	7.0	CW	1-2	1-3				
UNLESS OTHERWISE SPECIFIED, TOLERANCE IS ± DECIMALS HOLES ANGLES DRAFT .XX .049 .06 .002 1° 1-1/2° .XXX .005				TITEL: SPEC. CONTROL DWG. VARIABLE TRANSFORMER M5011CT								
MATERIAL :			ALL DIMENSIONS APPLY AFTER PLATING		DRAWN BY TIM RAU		DATE 8/20/97					
The information and design disclosed herein was originated by and is the property of STACO ENERGY PRODUCTS CO., which reserves all patent, proprietary, design, manufacturing, reproduction, use and sale rights thereto, and to any article disclosed therein except to the extent rights are expressly granted to others. The foregoing does not apply to vendor proprietary parts.				FIRST USED ON		DO NOT SCALE DWG.		CUSTOMER APPROVAL		DATE		
				CHECKER		DATE		WEIGHT APPROX. 78 LBS.		CODE IDENT. NO. 83008		DWG. NO. 031-6197
				ENGINEER		DATE		SCALE .5=1		SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Staco:

M5011CT