

# XCNT2118P16

limit switch XCNT - thermoplastic roller lever -  
1NC+1NO - snap - M16

Product availability: Non-Stock - Not normally stocked in distribution facility



## Main

|                               |                                                                                              |
|-------------------------------|----------------------------------------------------------------------------------------------|
| Commercial Status             | Commercialised                                                                               |
| Range of product              | OsiSense XC                                                                                  |
| Series name                   | Standard format                                                                              |
| Product or component type     | Limit switch                                                                                 |
| Device short name             | XCNT                                                                                         |
| Sensor design                 | Compact                                                                                      |
| Body type                     | Fixed                                                                                        |
| Head type                     | Rotary head                                                                                  |
| Material                      | Plastic                                                                                      |
| Body material                 | Plastic                                                                                      |
| Head material                 | Plastic                                                                                      |
| Fixing mode                   | By the body                                                                                  |
| Movement of operating head    | Rotary                                                                                       |
| Type of operator              | Spring return roller lever thermoplastic                                                     |
| Type of approach              | Lateral approach 2 directions                                                                |
| Cable entry                   | 2 entries tapped for M16 x 1.5 cable gland, cable outer diameter: 0.28...0.51 in (7...13 mm) |
| Number of poles               | 2                                                                                            |
| Contacts type and composition | 1 NC + 1 NO                                                                                  |
| Contacts operation            | Snap action                                                                                  |

## Complementary

|                                        |                                                                                                                                                                             |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Switch actuation                       | By 30° cam                                                                                                                                                                  |
| Electrical connection                  | Screw-clamp open terminals, clamping capacity: 1 x 0.34...2 x 1.5 mm²                                                                                                       |
| Contacts insulation form               | Zb                                                                                                                                                                          |
| Positive opening                       | With                                                                                                                                                                        |
| Positive opening minimum torque        | 1.33 lbf.in (0.15 N.m)                                                                                                                                                      |
| Minimum torque for tripping            | 0.88 lbf.in (0.1 N.m)                                                                                                                                                       |
| Maximum actuation speed                | 4.92 ft/s (1.5 m/s)                                                                                                                                                         |
| Contact code designation               | R300, DC-13 (Ue = 250 V, Ie = 0.1 A) conforming to EN/IEC 60947-5-1 appendix A<br>A300, AC-15 (Ue = 240 V, Ie = 3 A), Ithe = 10 A conforming to EN/IEC 60947-5-1 appendix A |
| [Ui] rated insulation voltage          | 300 V conforming to CSA C22.2 No 14<br>500 V degree of pollution 3 conforming to IEC 60947-1<br>300 V conforming to UL 508                                                  |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to IEC 60947-1<br>6 kV conforming to IEC 60664                                                                                                              |
| Short circuit protection               | 10 A cartridge fuse type gG                                                                                                                                                 |
| Mechanical durability                  | 10000000 cycles                                                                                                                                                             |
| Width                                  | 2.31 in (58.8 mm)                                                                                                                                                           |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the Schneider Electric group. It is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

|                                            |                                                                 |
|--------------------------------------------|-----------------------------------------------------------------|
| Shock resistance                           | 50 gn (duration = 11 ms) conforming to IEC 60068-2-27           |
| Vibration resistance                       | 25 gn (f = 10...500 Hz) conforming to IEC 60068-2-6             |
| IP degree of protection                    | IP65 conforming to IEC 60529                                    |
| IK degree of protection                    | IK04 conforming to EN 50102                                     |
| Class of protection against electric shock | Class II conforming to NF C 20-030<br>Class II                  |
| Ambient air temperature for operation      | -13...158 °F (-25...70 °C)                                      |
| Ambient air temperature for storage        | -40...158 °F (-40...70 °C)                                      |
| Protective treatment                       | TC                                                              |
| Product certifications                     | CCC<br>CSA<br>UL                                                |
| Standards                                  | EN/IEC 60204-1<br>EN/IEC 60947-5-1<br>UL 508<br>CSA C22.2 No 14 |

## Ordering and shipping details

|                       |                                                           |
|-----------------------|-----------------------------------------------------------|
| Category              | 22435 - LIMIT SWITCHES,TYPE XCM                           |
| Discount Schedule     | T                                                         |
| GTIN                  | 003389119047227                                           |
| Nbr. of units in pkg. | 10                                                        |
| Package weight(Lbs)   | 0.26                                                      |
| Product availability  | Non-Stock - Not normally stocked in distribution facility |
| Returnability         | N                                                         |
| Country of origin     | ID                                                        |

## Offer Sustainability

|                               |                                                                                       |
|-------------------------------|---------------------------------------------------------------------------------------|
| Sustainable offer status      | Not Green Premium product                                                             |
| RoHS                          | Compliant - since 1024 - <a href="#">Schneider Electric declaration of conformity</a> |
| REACH                         | Reference not containing SVHC above the threshold                                     |
| Product environmental profile | Available <a href="#">Download Product Environmental</a>                              |

## Contractual warranty

|        |           |
|--------|-----------|
| Period | 18 months |
|--------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XCNT2118P16](#)