

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT — By —

LOC

	DIST
--	------

REVISIONS

	F
--	---

LTR

DESCRIPTION

DATE _____

	DWN
--	-----

	APVD
--	------

BA 1

REVISÉD PER ECO-11-005150



21 MAR 11

RK

HMR

Technical Specification

Dissipation at 25°C	10 Watts Mounted on std heatsink
BS Ohmic Range	R01 to 10K
Stability	$\Delta R \leq 1\%$ per 1000hrs
Isolation Voltage	1400V DC/AC pk
Max Working Voltage	160 V DC/AC rms
Temp Coefficient	$<100R \pm 50 \text{ ppm}/^{\circ}\text{C}$ $>100R \pm 30 \text{ ppm}/^{\circ}\text{C}$
Climatic Category	55/200/56



RoHS Compliant

FOR A SPECIFIC PN FOR A RESISTANCE VALUE AND TOLERANCE, PLEASE REFER TO DMF.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	19SEPT06
-----	----------

R	BLANCH
CHK	19SEPT06

J	CATCHPOLE
ARVD	10SEPT06

J. CATCHPOLE
PRODUCT CREO

APPLICATION SPEC

[illegible]

TE Connectivity

6	NAME	THS10 METAL CLAD RESISTOR
---	------	---------------------------

SIZE	CAGE CODE	DRAWING NO.	RESTRICTED TO
------	-----------	-------------	---------------

A.3	00779	©-1879073
-----	-------	-----------

SCALE	NTS	SHEET	1 OF 1	REV	BA1
-------	-----	-------	--------	-----	-----

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[THS101R8J](#)