



CONVERSION CHART	
INCH	MM
.005	0.13
.015	0.38
.080	2.03
.091	2.30
.250	6.35
.460	11.68
.465	11.80
.579	14.70
.590	14.99
.700	17.78
.740	18.80
.810	20.57
.860	21.84
.898	22.8
.990	25.15
1.000	25.50
1.06	27.00
1.280	32.51
1.62	41.10



# SPECIFICATIONS:

MATERIALS:  
BODY: PHENOLIC, COLOR: BLACK.  
SHAFT HOLE INSERT: COPPER ALLOY.  
SET SCREW: STEEL.  
INLAY: ALUMINUM, SPUN FINISH.

# NOTES:

1. INTERPRET DRAWING PER ANSI Y14.5M-1982.
2. SUPPLIED WITH HEX HEAD, CUP POINT SET SCREWS ASSEMBLED.
3. BURRS CAUSED BY TAPPING MUST NOT INTERFERE WITH SHAFT INSERTION TO FULL SHAFT DEPTH NOR ARE THEY ALLOWED ABOVE OUTER SURFACE.
4. ALL CORNERS OR RADII TO BE .005 MAXIMUM.

MODEL NO.	DIMENSIONS						
	A DIA.	B DIA.	C DIA.	DIM. D	DIM. E	DIM. F	SHAFT HOLE DIA.
PKGP-70B-1/4	.740	.700	.590	.990	.080	.460	.250
PKGP-90B-1/4	.860	.810	.700	1.280	.080	.460	.250
PKGP-100B-1/4	1.06	1.000	.898	1.62	.091	.465	.250

<b>OUTLINE DRAWING</b>				SPECIFICATIONS ARE SUBJECT TO CHANGES WITHOUT NOTICE				THIS IS A C.A.D. GENERATED DRAWING. DO NOT MAKE MANUAL REVISIONS TO MASTER.			
 THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES DO NOT SCALE PRINT		ORIGINAL DATE OF DRAWING: 10-16-96		 452 JOHN DIETSCH BLVD. ATTLEBORO FALLS, MASS. 02763 INC.					
				DRAWN: S.KIRCORIAN DATE: 10-16-96							
TOLERANCES (EXCEPT AS NOTED) ANGULAR = ±1° DECIMAL .XX = ± DECIMAL .XXX = ±.015 DECIMAL .XXXX = ±		FILE NAME: 80779OUT DIRECTORY: KNOBS		CHECKED:		DATE:		TITLE: <b>OUTLINE DRAWING</b> <b>KNOB</b> <b>(PKGP) SERIES</b>			
				MATERIAL: SEE SPECIFICATIONS		APPROVED: <i>[Signature]</i> DATE: 10-21-96					
AUGAT CONFIDENTIAL This document contains information which is the exclusive property of Augat Inc. Distribution, reproduction or use by others is not permitted without the expressed written consent of Augat Inc.		FINISH: SEE SPECIFICATIONS		CODE IDENT. NO. 91506		DATE: 10-21-96		DWG. NO. 80779-SD PRODUCT CODE: M12			
				NEXT ASSY:		DWG. SIZE C					
				SCALE:		SHEET 1 OF 1					

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[PKGP90B1/4](#)