


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	11-10	@20°C
D.C. RESISTANCE	3-2	@20°C
D.C. RESISTANCE	7-6	@20°C
D.C. RESISTANCE	10-9	@20°C
D.C. RESISTANCE	4-3	@20°C
INDUCTANCE	7-6	10kHz, 100mVAC, Ls
SATURATION CURRENT		20% rolloff from initial
LEAKAGE INDUCTANCE	7-6	tie(2+3+4+9+10+11), 100kHz, 100mVAC, Ls
DIELECTRIC	7-9	tie(2+11), 1875VAC, 1 second
URNS RATIO		(7-6):(11-10)
URNS RATIO		(7-6):(3-2)
URNS RATIO		(7-6):(10-9)
URNS RATIO		(7-6):(4-3)
URNS RATIO		(3-2):(4-3)



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:

- Functional insulation.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications		Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
		Method: Tape & Reel		Angles: $\pm 1^\circ$	TRANSFORMER	
		PKG-0757		Fractions: $\pm 1/64$		
6B	2/15	www.we-online.com/midcom	CONVENTION PLACEMENT	Decimals: $\pm .005$ [.13]		750314459
6A	9/14	SEE REVISION SHEET FOR REVISION LEVEL		Footprint: $\pm .005$ [.13]	eiSos p/n: 750314459	SPECIFICATION SHEET 1 OF 1



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Würth Electronics:](#)

[750314459](#)